


PART



CUTOUT

NOTES:

1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
2. DIMENSIONS IN [] ARE METRIC.
3. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
4. MATERIAL:
ENCLOSURE: POLYAMIDE 6
SEAL - NBR/EPDM
5. PROTECTION CLASS WHEN USED WITH CEG GROMMETS:
NEMA 1,12
IP 65
6. TEMPERATURE RANGE: -22 - 212 °F
7. FLAMMABILITY: V0
8. RoHS COMPLIANT
9. COMPLIANCE: cURus
10. UV RESISTANT
11. WEIGHT: SEE TABLE



PART NUMBER	GL	D	S	INSTALLATION HEIGHT (EH)	SW1/SW2	NUMBER OF OPENINGS			THREAD METRIC	CUTOUT DIA. (d)	PART WEIGHT	PKG QTY
	in. (mm)	in. (mm)	in. (mm)			in. (mm)	SMALL	MEDIUM		LARGE		
CEST2-RL251	0.59 (15)	1.57 (40)	0.405 (10)	0.73 (18.5)	1.42/1.10 (36/28)	1	-	-	M25x1.5	1.00 (25.50)	0.053 (24.0)	5
CEST2-RL321	0.59 (15)	1.97 (50)	0.405 (10)	0.71 (18)	1.81/1.42 (46/36)	-	1	-	M32x1.5	1.28 (32.50)	0.062 (28.0)	5
CEST2-RL401	0.79 (20)	2.44 (62)	0.485 (12)	0.71 (18)	2.17/1.81 (55/46)	-	1	-	M40x1.5	1.59 (40.50)	0.116 (52.5)	5
CEST2-RL501	0.79 (20)	2.44 (62)	0.485 (12)	0.87 (22)	2.17/2.17 (55/55)	-	-	1	M50x1.5	1.99 (50.50)	0.134 (61.0)	5

PART NUMBER		SEE TABLE	
TITLE		CEST2-RL Control Drawing	
		CUSTOMER DRAWING	
ITEM REVISION NAME		00872EBG/00	
DATASET FILE NAME		00872EBG_DC/00A	
		THIRD ANGLE PROJECTION	
MATERIAL		SEE NOTE 4	
DRAWING NUMBER		00872EBG - DC	
DRAWN BY	DATE	CHK	SCALE
SERH	9/13/2022	MDS	1:1
SHEET 1 OF 1		B	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00A	9/13/2022	SERH	MDS	JADE	INITIAL RELEASE	124032/00

B

B

A

A

B-SIZE CUSTOMER