


PART



CUTOUT

NOTES:

1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
2. DIMENSIONS IN [] ARE METRIC.
3. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
4. MATERIAL:
 FRAME - POLYPROPYLENE (PP)
 BLOCK - TPE
5. PROTECTION CLASS:
 NEMA 12,4x**
 IP 66
6. TEMPERATURE RANGE: -22 - 158 °F
7. FLAMMABILITY: HB
8. RoHS COMPLIANT
9. COMPLIANCE: cURus
10. UV RESISTANT
11. WEIGHT: SEE TABLE

**Indoor Use & Horizontal Mounting



PART NUMBER	A	B	C	NUMBER OF OPENINGS		THREAD METRIC	D	PART WEIGHT	PKG QTY
	in. (mm)	in. (mm)	in. (mm)	TOTAL	NUMBER X DIA.		in. (mm)	lbs. (g)	
CESUM3-R406	1.91 (48.50)	0.33 (8.50)	0.47 (12.00)	6	1 x 0.079 - 0.157 (1 x 2 - 4)	M40x1.5	1.59 (40.5)	0.99 (45)	5
					2 x 0.12 - 0.24 (2 x 3 - 6)				
					2 x 0.20 - 0.35 (2 x 5 - 9)				
					1 x 0.3 - 0.47 (1 x 7.5 - 12)				
CESUM3-R407	1.91 (48.50)	0.33 (8.50)	0.47 (12.00)	7	4 x 0.12 - 0.24 (4 x 3 - 6)	M40x1.5	1.59 (40.5)	0.99 (45)	5
					3 x 0.20 - 0.35 (3 x 5 - 9)				

PART NUMBER		SEE TABLE	
TITLE			
CESUM3-RL Control Drawing			
CUSTOMER DRAWING			
ITEM REVISION NAME		00872EBK/00	
DATASET FILE NAME		00872EBK_DC/00A	
		THIRD ANGLE PROJECTION	
MATERIAL		SEE NOTE 4	
DRAWING NUMBER		00872EBK - DC	
DRAWN BY	DATE	CHK	SCALE
SERH	9/13/2022	MDS	1:1
SHEET 1 OF 1			SIZE B

00A	9/13/2022	SERH	MDS	JADE	INITIAL RELEASE	124032/00
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

B

B

A

A

B-SIZE CUSTOMER