




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



12 PORT SHOWN



NOTES:

1. SEE CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN BRACKETS ARE METRIC [mm].
4. PART INCLUDES:
 - (1) ENCLOSURE PRELOADED WITH (6, 12, 24 or 48) DUPLEX MULTIMODE, SINGLEMODE SC OR E2000 ADAPTERS.
 - (1) HARDWARE KIT CONTAINING:
 - (4) M6 x 12mm SCREWS (10029-01)
 - (4) #12-24 x 1/2" SCREWS (34466-22)
 - (2) FIBER SLACK SPOOL (RFMS1)
 - (1) 2 FIBER ENTRY GROMMETS (00466-02)
 - (1) PG-11 GLAND (00001-141)
 - (2) PAN-TY CABLE TIES (PLT2S-M0)
 - (1) FIBER CAUTION LABEL
 - (1) LASER WARNING LABEL

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
03B	10-18-22	SAT	JSP	ANJA	D. ADDED P/N's FD1W6E1DSCZ, FD1W6AGDSCZ, FD1W12E1DSCZ, FD1W12AGDSCZ, FD1W24E1DSCZ, FD1W24AGDSCZ, FD1W12E1DLCZ, FD1W12AGDLCZ, FD1W24E1DLCZ, FD1W24AGDLCZ.	F10431AJ-DC
03A	07-14-22	SAT	JSP	ANJA	C. REMOVED E2000 PRODUCT, OBSOLETE. B. REMOVED ALL PHOS BRONZE P/N's. A. ADDED P/N FD1W48BUDLCZ.	F10431AJ-DC
00	03-16-17	SAT	BSN	DFP	RELEASED TO PRODUCTION	F10431AJ-DC

TITLE		FD1 FIBER DRAWER WITH OPTIONAL ADAPTER ASSEMBLY	
CUSTOMER DRAWING			
ITEM REVISION NAME		F10431AJ/03	
DATASET FILE NAME		F10431AJ_DC/03B	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		PART NO.	
.x ±	.xxx ± .010 [0.3]	SEE SHEET 2 & 3	
.xx ± .03 [0.8]	ANGLES ±	DRAWING NUMBER:	
THIRD ANGLE PROJECTION		F10431AJ-DC	
DRAWN BY	DATE	CHK	SCALE
SAT	3-13-17	BSN	NONE
SHT 1 OF 3		SIZE	
		A	

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

DUPLEX SC					
PART NUMBER	ADAPTER COLOR	SPLIT SLEEVE TYPE	APPLICATION	NUMBER OF PORTS	WEIGHT
FD1W6AQDSCZ	AQUA	ZIRCONIA	50/125 OM3	6	6.5 LBS (2948g)
FD1W6BUDSCZ	BLUE	ZIRCONIA	9/125 OS2		
FD1W6EIDSCZ	ELECTRIC IVORY	ZIRCONIA	62.5/125 OM1		
FD1W6AGDSCZ	APC GREEN	ZIRCONIA	9/125 OS2		
FD1W12AQDSCZ	AQUA	ZIRCONIA	50/125 OM3	12	
FD1W12BUDSCZ	BLUE	ZIRCONIA	9/125 OS2		
FD1W12EIDSCZ	ELECTRIC IVORY	ZIRCONIA	62.5/125 OM1		
FD1W12AGDSCZ	APC GREEN	ZIRCONIA	9/125 OS2		
FD1W24AQDSCZ	AQUA	ZIRCONIA	50/125 OM3	24	
FD1W24BUDSCZ	BLUE	ZIRCONIA	9/125 OS2		
FD1W24EIDSCZ	ELECTRIC IVORY	ZIRCONIA	62.5/125 OM1		
FD1W24AGDSCZ	APC GREEN	ZIRCONIA	9/125 OS2		

B

B




A

A

SEE SHEET 1 FOR REVISION HISTORY

TITLE FD1 FIBER DRAWER WITH OPTIONAL ADAPTER ASSEMBLY CUSTOMER DRAWING			
ITEM REVISION NAME F10431AJ/03			
DATASET FILE NAME F10431AJ_DC/03B			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)			
.x ± .xx ± .03 (0.8)		.xxx ± .010 (0.3)	
ANGLES ±			
DRAWN BY SAT		DATE 3-13-17	
CHK BSN		SCALE NONE	
DRAWING NUMBER: F10431AJ-DC		PART NO. SEE SHEET 2 & 3	
REV		DATE	
BY		CHK	
APR		DESCRIPTION	
ECN		SHT 2 OF 3	
SIZE A			




THIRD ANGLE PROJECTION

2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

DUPLEX LC					
PART NUMBER	ADAPTER COLOR	SPLIT SLEEVE TYPE	APPLICATION	NUMBER OF PORTS	WEIGHT
FD1W12AQDLCZ	AQUA	ZIRCONIA	50/125 OM3	12	6.5 LBS (2948g)
FD1W12BUDLCZ	BLUE	ZIRCONIA	9/125 OS2		
FD1W12EIDLDCZ	ELECTRIC IVORY	ZIRCONIA	62.5/125 OM1		
FD1W12AGDLCZ	APC GREEN	ZIRCONIA	9/125 OS2		
FD1W24AQDLCZ	AQUA	ZIRCONIA	50/125 OM3	24	
FD1W24BUDLCZ	BLUE	ZIRCONIA	9/125 OS2		
FD1W24EIDLDCZ	ELECTRIC IVORY	ZIRCONIA	62.5/125 OM1		
FD1W24AGDLCZ	APC GREEN	ZIRCONIA	9/125 OS2		
FD1W48BUDLCZ	BLUE	ZIRCONIA	9/125 OS2	48	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	TITLE FD1 FIBER DRAWER WITH OPTIONAL ADAPTER ASSEMBLY CUSTOMER DRAWING					
							ITEM REVISION NAME F10431AJ/03				PANDUIT	
							DATASET FILE NAME F10431AJ_DC/03B					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) .X ± .xxx ± .010 (0.3) .XX ± .03 (0.8) ANGLES ±				PART NO. SEE SHEET 2 & 3	
					SEE SHEET 1 FOR REVISION HISTORY		 THIRD ANGLE PROJECTION				DRAWING NUMBER: F10431AJ-DC	
							DRAWN BY SAT	DATE 3-13-17	CHK BSN	SCALE NONE	SHT 3 OF 3	SIZE A

2

1