


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

- **1. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AND TO INDICATE COLOR AND OR PACKAGE QUANTITY.
- 2. SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
- 3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
- 4. CABLE MEETS CATEGORY 6 REQUIREMENTS.
- 5. ALL MATERIALS AND COMPONENTS USED MUST MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.

TWIST TIE



WITH PLUG CAPS

PANDUIT PART NUMBER	MIN. CABLE LENGTH	WEIGHT
ISTPSP1MBL	1 M	1.82 lbs/10 PCS (825.8 g/10 PCS)
ISTPSP2MBL	2 M	3.64 lbs/10 PCS (1651.6 g/10 PCS)
ISTPSP3MBL	3 M	5.46 lbs/10 PCS (2477.5 g/10 PCS)
ISTPSP5MBL	5 M	9.10 lbs/10 PCS (4129.1 g/10 PCS)

WITHOUT PLUG CAPS

PANDUIT PART NUMBER	MIN. CABLE LENGTH	WEIGHT
ISTPSPNC1MBL	1 M	1.53 lbs/10 PCS (692.84 g/10 PCS)
ISTPSPNC2MBL	2 M	1.99 lbs/10 PCS (901.84 g/10 PCS)
ISTPSPNC3MBL	3 M	2.45 lbs/10 PCS (1110.84 g/10 PCS)
ISTPSPNC5MBL	5 M	4.28 lbs/10 PCS (1939.41 g/10 PCS)

T568B WIRING

PLUG POSITION	CABLE WIRE
1	WHITE ORANGE
2	ORANGE
3	WHITE GREEN
4	BLUE
5	WHITE BLUE
6	GREEN
7	WHITE BROWN
8	BROWN

PLUG CAPS - ON ISTPSP*MBL PARTS ONLY

MODEL FILENAME	SIZE
DRAWING FILENAME	A
M024790D_DC392/00A	
CATEGORY 6 INDUSTRIALNET, SFTP, STRANDED, PATCH CORDS WITH AND WITHOUT PANDUIT PLUG CAPS CUSTOMER DRAWING	
PANDUIT [®] TINLEY PARK, IL 60487	I.I. NUMBER
	PRODUCT SPEC/ PKG SPEC
THIRD ANGLE PROJECTION	ASSY METHOD/ TEST METHOD
ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ±.03(.8)(.XXX) ±.01(1.3) (.XX) ± ANGLES ±	SCALE
	NONE
DRAWN BY BJN	REVIEW DRAWING NUMBERS
DATE 3-15-11	PART NO.
CHK'D MBVE	ISTPSP*MBL ISTPSPNC*MBL
	DRAWING NO.
	02479-392

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
R	3-15-11	BJN	MBVE	RELEASED TO PRODUCTION	02479-392		RDE		