


# specifications

The Wire Basket Overhead Cable Tray Routing System shall consist of pathway sections, splice connectors, sidewalls, waterfalls, mounting brackets, and accessories designed to route and manage copper, fiber optic, or power cables. The pathway sections shall be provided in the various widths: 4", 6", 8", 12", 18", 24". The baskets are 118.33 inches long and are available in 2", 4", or 6" sidewall heights. Trapeze, cantilever, and wall mount brackets are available to support the system. Baskets, accessories, and components are available in black, electro zinc, and white.



### technical information


Material:	Black (BL) and White (WH): Steel wire, powder coated black, or white	
	Electro Zinc (EZ): Steel wire electro zinc plated	
Approvals:	UL Listed for their suitability for use as Equipment Grounding Conductor in accordance with Sections 392.6(A) and 392.6(B) of the NFPA 70 National Electric Code with AMD 1-5 and NEMA VE1.	
	Black and White: Complies with ASTM 510	
	Electro Zinc: ASTM B633 SC1, Type III	

## key features and benefits

Strength to weight ratio:	The design of the Wire Basket Pathway Sections provides a greater strength-to-weight ratio than competitive wire basket; easier handling translates into faster installation	
Grid pattern:	The wire mesh grid pattern allows greater amounts of cables and QuickNet® Cassettes to pass grid openings without additional cutting, reducing installation time	
Wire:	Maintain better safe working load than those in the market with the use of less wires. Less wire means less cutting which aids in reducing the sharp edges	
Waterfalls:	Cable exit that provides proper bend radius control and are available in various sizes	
Bend radius control intersection:		
Splices:	Various Splices available which include the following: expansion splice, tool-less splice, and bolted splice	


## applications

The Wire Basket Overhead Cable Tray Routing System is designed to route and manage copper data cables, fiber optic, or power cables within data centers, connected buildings, and industrial automation applications. Innovative features provide quick, safe, and easy assembly for reduced installation costs and faster deployment.



#### 1. Select Your Basket Tray Size

	= =,=		
	Basket Height	Basket Width	Color
PWI	2 = 2 inch 4 = 4 inch 6 = 6 inch	X4 = 4 inch X6 = 6 inch 1 X8 = 8 inch 2 X12 = 12 inch 3 X18 = 18 inch 4 X24 = 24 inch	BL = Black WH = White EZ = Electro Zinc



Note: All pathway sections are 118.33 inches long.

#### 2. Select A Mounting Option

	Basket Type	Basket Width	Color
	<b>5 6 7 TB</b> = Trapeze Bracket <sup>1</sup>	<b>4</b> = 4 inch	
	8 CB = Cantilever Bracket <sup>1</sup>	<b>6</b> = 6 inch	<b>BL</b> = Black
PWB	WMBV = Vertical Wall Mount Bracket	<b>8</b> = 8 inch <b>12</b> = 12 inch	<b>WH</b> = White
	<b>WMN</b> = Narrow Termination Bracket	<b>18</b> = 18 inch	<b>EZ</b> = Electro Zinc
	9 WMW = Wide Termination Bracket	<b>24</b> = 24 inch	



<sup>1</sup>Only required for trapeze and cantilever bracket options

#### 3. Select Your Hardware

	Series	Color
	10 SPL = Bolted Splice	
	PS = Push-On Splice	DI Disale
PWB	FES = Expansion Splice	BL = Black WH = White
	TSB = Trapeze Hanging Clip <sup>2</sup>	<b>EZ</b> = Electro Zinc
	SC = Strut Clip <sup>2</sup>	LZ - Liectro Ziric
	<b>HK</b> = Hardware Kit Clip <sup>3</sup>	



<sup>&</sup>lt;sup>2</sup>Available only in electro-zinc plating (EZ)

<sup>&</sup>lt;sup>3</sup>Available only in black and electro-zinc (BL and EZ)

#### 4. Configure Your Intersections

	Series	Basket Height Used	Basket Width Used <sup>4</sup>	Color
PWB	11 IB = 90° Radius Intersection⁴ 12 PF = Formed Tee Fitting	2 = 2 inch 4 = 4 inch 6 = 6 inch	X4 = 4 inch X6 = 6 inch X8 = 8 inch X12 = 12 inch X18 = 18 inch X24 = 24 inch	BL = Black WH = White EZ = Electro Zinc



#### 5. Add Your Waterfalls

	Series	Color
	13 DOK = Drop Out Kit	
	WFN = Narrow Waterfall	<b>BL</b> = Black
PWB	<b>WFW</b> = Wide Waterfall	<b>WH</b> = White
	SPJ2 = Spillover Exit 2" <sup>5</sup>	<b>EZ</b> = Electro Zinc
	<b>15</b> SPJ4 = Spillover 4"5	



#### 6. Select A Tray Liner

	Series	Basket Width Used	Color
PWB	6 TL = Tray Liner	4 = 4 inch 6 = 6 inch 8 = 8 inch 12 = 12 inch 18 = 18 inch 24 = 24 inch	BL = Black WH = White PG = Pre-Galvanized



#### 7. Select A Divider Wall

	Series	Basket Width Used	Color
		<b>2</b> = 2 inch	<b>BL</b> = Black
PWB	17 DW = Divider Wall	<b>4</b> = 4 inch	<b>WH</b> = White
		<b>6</b> = 6 inch	<b>PG</b> = Pre-Galvanized



<sup>&</sup>lt;sup>4</sup>Skip this for IB series part numbers (not required)

<sup>&</sup>lt;sup>5</sup>Available only in black (BL)

## commonly ordered part examples

#### **Basket Trays**

Part Number	Basket Height	Basket Width	Color
PWB2X24EZ	2"	24"	Electro Zinc
PWB4X12BL	4"	12"	Black
PWB4X18EZ	4"	18"	Electro Zinc

#### **Mounting Brackets**

Part Number	Bracket Type	Support Width	Color
PWBTB12EZ	Trapeze	12"	Electro Zinc
PWBCB18BL	Cantilever	18"	Black
PWBWMBVBL	Wall Mount Vertical	Supports All Widths	Black
PWBWMNEZ	Narrow Termination	Supports 4" and 12"	Electro Zinc
PWBWMWEZ	Wide Termination	Supports 6", 8", 18", and 24"	Electro Zinc

#### Hardware

Part Number	Service	Support Width	Color
PWBSPLBL	Bolted Splice	Supports All Widths	Black
PWBPSEZ	Push on Splice	Supports All Widths	Electro Zinc
PWBTSBEZ	Trapeze Hanger Clip	Supports 4", 6", 8", and 12"	Electro Zinc
PWBSCEZ	Strut Clip	Supports All Widths	Electro Zinc
PWBHKBL	Hardware Kit Clip	Supports All Widths	Black

#### Intersection

Part Number	Series	Basket Height	Support Width	Color
PWBIB2BL	90° Radius Intersection	2"	Supports All Widths	Black
PWBPF4X12EZ	Formed Tee Intersection	4"	12"	Electro Zinc

#### Waterfall

Part Number	Service	Support Width	Color
PWBDOKBL	Drop Out Kit	Supports All Widths	Black
PWBWFNEZ	Narrow Waterfall	Supports All Widths	Electro Zinc
PWBWFWBL	Wide Waterfall	Supports 8" and Up	Black
PWBSPJ2BL	Spillover Exit 2"	Supports All Widths	Black
PWBSPJ4BL	Spillover Exit 4"	Supports All Widths	Black

#### **Tray Liner**

Part Number	Service	Support Width	Color
PWBTL12BL	Tray Liner	12"	Black
PWBTL18PG	Tray Liner	18"	Pre-Galvanized

#### **Divider Wall**

Part Number	Service	Support Width	Color
PWBDW2BL	Divider Wall	2"	Black
PWBDW4PG	Divider Wall	4"	Pre-Galvanized

**WORLDWIDE SUBSIDIARIES AND SALES OFFICES** 

PANDUIT US/CANADA Phone: 800.777.3300 PANDUIT EUROPE LTD. London, UK Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore Phone: 65.6305.7575 PANDUIT JAPAN Tokyo, Japan Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Guadalajara, Mexico Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

