


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

TWIST TIE



PANDUIT PART NUMBER	MIN. CABLE LENGTH	WEIGHT
ISTPCHNC1MBLY	1 M	1.72 lbs/10 PCS (779.4 g/10 PCS)
ISTPCHNC2MBLY	2 M	3.44 lbs/10 PCS (1558.8 g/10 PCS)
ISTPCHNC3MBLY	3 M	5.15 lbs/10 PCS (2338.2 g/10 PCS)
ISTPCHNC4MBLY	4 M	6.87 lbs/10 PCS (3117.5 g/10 PCS)
ISTPCHNC5MBLY	5 M	8.59 lbs/10 PCS (3896.9 g/10 PCS)

NOTES:



- \*\*1. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AND TO INDICATE COLOR AND OR PACKAGE QUANTITY.
- 2. SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
- 3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
- 4. CABLE MEETS CATEGORY 5E REQUIREMENTS AND CURRENT ODVA REQUIREMENTS FOR INDUSTRIAL CABLE.
- 5. ALL MATERIALS AND COMPONENTS USED MUST MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.

T568A WIRING

PLUG POSITION	CABLE WIRE
1	WHITE GREEN
2	GREEN
3	WHITE ORANGE
4	BLUE
5	WHITE BLUE
6	ORANGE
7	WHITE BROWN
8	BROWN

SIZE

A

DRAWING FILENAME		M02479PJ_DC372_00A.PRT
CATEGORY 5E INDUSTRIALNET, SFTP, SOLID, PATCH CORDS WITHOUT PANDUIT PLUG CAPS CUSTOMER DRAWING		
 <b>PANDUIT</b> <sup>R</sup> CORP. TINLEY PARK, IL 60477	I.I. NUMBER	
	PRODUCT SPEC	
 THIRD ANGLE PROJECTION ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ± .03(.8) (.XXX) ± .010(.3) (.XX) ± .005 ANGLES ±	WORK INSTRUCTION	
	SCALE	NONE
DRAWN BY	MDJr	REVIEW DRAWING NUMBERS
DATE	4-22-04	PART NO.
CHK'D		ISTPCHNC*MBLY
		DRAWING NO.
		02479-372

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
R	4-11-07	MDJr		RELEASED TO PRODUCTION	02479-372				