



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NUMBER	WEIGHT
NKA6PPG24Y	1.26 lb (572.73 g)

- NOTES:
- SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AS WELL AS OPTIONAL ICONS.
  - MATERIAL:  
 PANEL HOUSING: STEEL  
 RJ45 MODULES: THERMOPLASTIC RESIN UL94V-0  
 PUNCHDOWN BLOCKS: THERMOPLASTIC RESIN UL94V-0  
 BEZEL ASSEMBLY: THERMOPLASTIC RESIN UL94H-B  
 RETENTION CAP: THERMOPLASTIC RESIN UL94V-0
  - 24 PORT ANGLED PATCH PANEL 8 POSITION 8 WIRE.
  - THE PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
  - FOUR (4) 12-24 X 1/2" ROUND HEAD SCREWS ARE PROVIDED FOR FASTENING TO RACKS.
  - DIMENSIONS IN BRACKETS ARE IN METRIC.
  - USE 110 STYLE TERMINATION TOOL FOR PUNCHDOWN.
  - RETENTION CAPS (ONE PER CONNECTOR) PROVIDED FOR SNAP-IN ON TERMINATED CONNECTORS.



CID\*\*-C & CIP\*\*-C, PHONE OR DATA ICON LOCATES HERE. IDENTIFIES INDIVIDUAL PORT. OPTIONAL, NOT SUPPLIED.

PART NUMBER	SEE CHART	PRODUCT SPEC/PKG SPEC	N/A
I.I. NUMBER	N/A	WORK INSTRUCTION	N/A

TITLE  
**NETKEY CAT6 24 PORT ANGLED PATCH PANEL**  
 CUSTOMER DRAWING

ITEM REVISION NAME	M02088AL/01	<b>PANDUIT</b>
DATASET FILE NAME	M02088AL_DC24/01A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		MATERIAL:
.x ± .1 [2.54]	.xxx ± .005 [0.127]	DRAWING NUMBER: 02088-42
.xx ± .01 [0.25]	ANGLES ± 5°	
THIRD ANGLE PROJECTION		

2	10-1-18	BAME	KRKE	MMR	A. REMOVED M6 SCREWS	M09000HW
1	10-2-13	BJN	SCAL	JCK	ADDED NEW PANDUIT TITLE BLOCK	02088-42
R	1-23-13	LZ	MBVE	MBVE	RELEASED TO PRODUCTION	02088-42

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
-----	------	----	-----	-----	-------------	-----

DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
LZ	1-22-13	MBVE	.25:1		A

D101000DA/14