



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.





COVER REMOVED FOR CLARITY



PANDUIT P/N	WEIGHT
CUFMB24BL	2.12 LB/EACH PC (961.6 g/EACH PC)

NOTES:

- SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
- SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
- DIMENSIONS IN PARENTHESES ARE IN METRIC.
- PART INCLUDES:
 - 1- METAL BODY
 - 4- 6 POSITION FACEPLATE
 - 1- FACEPLATE LABEL/LABEL COVER KIT WHICH INCLUDES:
 - 4 LABELS AND 4 LABEL COVERS
 - 1- COVER
 - 4- TAK-TY
 - 1- 48 PORT IDENTIFICATION LABEL
 - 2- CABLE ENTRY GROMMETS



REMOVABLE GROMMET PLATE FOR GREATER CABLE DENSITY



PART NUMBER		CUFMB24BL	
TITLE			
MINI-COM 24 PORT CONSOLIDATION BOX			
CUSTOMER DRAWING			
ITEM REVISION NAME		M01032AA/04	
DATASET FILE NAME		M01032AA_DC/04C	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		MATERIAL:	
.X ± .XX ± .03 (.8)		.XXX ± .010 (.3)	
ANGLES ±		.060" ALUMINUM	
DRAWN BY		DRAWING NUMBER:	
JSP		01032-16	
DATE		SHT 1 OF 1	
8-31-01		A	
CHK		SCALE	
AMYR		NONE	
THIRD ANGLE PROJECTION			

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
04C	5-4-23	BJN	BSN	TAM	RELEASED FOR PRODUCTION	01032-16

D10100DA/14