

Total Routing Solution



PANDUIT offers the most complete line of non-metallic surface raceway. PAN-WAY® Surface Raceway provides maximum flexibility for routing both power and data cabling, seamlessly integrated for a total routing solution.

- *PAN-WAY®* Power Rated Raceway Systems provide extreme tamper resistance, yet are accessible for cost effective moves, adds, and changes
- *PAN-WAY®* Fittings are designed to maintain the TIA/EIA 568-B and 569-B required minimum bend radius for high performance copper and fiber optic cabling systems in data applications
- Snap-On Faceplates and *FAST-SNAP™* Boxes install without the use of screws for faster installation and superior aesthetics
- Exclusive *PAN-WAY®* T-70 *WORKSTATION OUTLET CENTER™* with Snap-On Faceplates facilitate installation, provide maximum cable capacity, and can be easily positioned to meet workstation requirements
- The complete line of power rated raceways, fittings, outlet boxes and accessories comply with stringent UL5A and CSA C22.2 No. 62.1-03 approvals for use up to 600 V



Snap-On Faceplates with
FAST-SNAP™ Boxes



T-70 *WORKSTATION
OUTLET CENTER™*



T-70 Raceway with
Snap-On Faceplates

PANDUIT is a Global Leader Providing Innovative End-To-End Network Connectivity Solutions that Enable the Deployment of Technology.

- *Raceway Systems*
- *Copper Cabling Systems*
- *Fiber Cabling Systems*
- *Outlets*
- *Zone Cabling Systems*
- *Network Management and PoE Systems*
- *Fiber Routing Systems*
- *Racks and Cable Management*
- *Network Grounding Systems*
- *Network Identification Systems*
- *Network Cable Ties and Accessories*

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com
or by phone: 800-777-3300 and reference ad #

