



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	KEY	COLOR	WEIGHT	FERRULE TYPE
FJJSMM5CYOR	Y	ORANGE	.29 LB/10 PCS (134.0 g/10 PCS)	ZIRCONIA (CERAMIC)



NOTES:

- SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE PACKAGE QUANTITY.
- SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
- DIMENSIONS IN PARENTHESES ARE IN METRIC.
- MATERIAL;
 -BOOTS: ELASTOMER
 -JACK COVER: PC/ABS
 -CRIMP SLEEVE: BRASS
 -FERRULE: ZIRCONIA (CERAMIC)
 -JACK HOUSING: PC/ABS
 -JACK DUST CAP: ELASTOMER



KEYED "Y"
CONFIGURATION

SCALE: 2 : 1

CAD FILENAME/LAYERS		M00977AM_DC_00A.prt	
PANDUIT CORP. TINLEY PARK, ILLINOIS			
OPTI-CRIMP™ FJ KEYED "Y" MULTIMODE MODULE (FJJSMM5CYOR) CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ±.010(.3) (.XX) ±.03(.8) ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY MC	MAT'L:	SCALE NONE	
DATE 07-10-01	SEE NOTES	DRAWING NO.	DWG SIZE
CHECKED BY		00977-39	A

REV	DATE	BY	CHK	DESCRIPTION	ECN	CHK	CUST	SUP
R	07-17-01	MC		RELEASED TO PRODUCTION	00977-39			