




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



ABOVE VIEWS
(SHOWN W/O DUST CAP)



OUTER HOUSING EXPLODED ISOMETRIC VIEW
SCALE: .75 : 1

PANDUIT P/N	FIBER SIZE (MICRONS)	WEIGHT
FSCMM**	62.5/125	.082 lb/10 PCS (37.0 g/10 PCS)
FSCMM50**	50/125	.082 lb/10 PCS (37.0 g/10 PCS)

NOTES:

- SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
- MATERIALS:
 - A. OUTER HOUSING: POLYETHERIMIDE
 - B. BOOTS: THERMOPLASTIC ELASTOMER
 - C. CRIMP SLEEVE: BRASS
 - D. INNER HOUSING ASSEMBLY:
 - a. INNER HOUSING: POLYCARBONATE
 - b. SPRING: STAINLESS STEEL
 - c. BACKBONE: NICKEL PLATED BRASS
 - d. FERRULE HOLDER: ALUMINUM
 - e. FERRULE: ZIRCONIA (CERAMIC)
- COMPLIES WITH THE FIBER OPTIC PERFORMANCE REQUIREMENTS AS SPECIFIED IN TIA/EIA 568-A AND B.3
- COMPLIES WITH FOCIS-3 (TIA/EIA 604-3)
- DIMENSIONS IN PARENTHESIS ARE METRIC.

DRAWING FILENAME	M01241AA_DC_01A.PRT (1)	SIZE	A
------------------	-------------------------	------	---

OPTI-CRIMP™ SC MULTIMODE PRE-POLISHED CRIMP FIBER OPTIC CONNECTOR (FSCMM**/FSCMM50**) CUSTOMER DRAWING

<p>THIRD ANGLE PROJECTION</p>	<p>ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.</p> <p>DIMENSIONAL TOLERANCES ARE: (.X) ±.2 (.XXX) ±.010 (.XX) ±.03 ANGLES ± 1°</p>	I.I. NUMBER
		PRODUCT SPEC
<p>DRAWN BY MC</p> <p>DATE 10-11-01</p> <p>CHK'D</p>	<p>MAT'L:</p> <p>SEE NOTES</p>	WORK INSTRUCTION
		SCALE
		PART NO.
		FSCMM** FSCMM50**
		DRAWING NO.
		01241-06

R	10-11-01	MC		RELEASED TO PRODUCTION	01241-06						
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH			