



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
FJJFRL-X	.032 LB/10 PCS (14.3g/10 PCS)



NOTES:

- SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
- SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
- DIMENSIONS IN PARENTHESES ARE IN METRIC.
- KIT CONTAINS:
 - (10) - FERRULE AND DOUBLE FLANGED JACK FERRULE HOLDER ASSEMBLIES (FJMMFA)
 - (10) - GOF CRIMP SLEEVE (FJ-GCS)
- MATERIAL:
 - CRIMP SLEEVE - PLATED BRASS
 - FERRULE ASSEMBLY:
 - DUST CAP - RUBBER
 - FERRULE HOLDER - PLATED BRASS
 - FERRULE - ZIRCONIA CERAMIC
- FERRULE DIAMETER: 2.498/2.500mm.



ISOMETRIC VIEW

SCALE: 1 : 1

CAD FILENAME/LAYERS		M35787AO_DC_00A.PRT	
PANDUIT CORP. TINLEY PARK, ILLINOIS			
OPTI-JACK FERRULE REPLACEMENT WITH CRIMP SLEEVES (FJJFRL-X) CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .010 (.3) (.XX) ± .03 (.8) ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY MC	MAT'L:	SCALE 2 : 1	
DATE 07-11-01	SEE NOTES	DRAWING NO.	DWG A
CHECKED BY		35787-49	SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN	CHK	CUST	SUP
R	07-11-01	MC		RELEASED TO PRODUCTION	35787-49			