


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
CUFB48BL	7.12 LB/EACH PC (3230 G/EACH PC)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
4. PART INCLUDES:
 - 1- METAL BODY
 - 2- PASS THRU ASSEMBLY (WITH TWO SCREWS)
 - 6- 8 POSITION INSERT
 - 4- GROMMET
 - 1- COVER
 - 6- TAK-TY™
 - 1- 48 PORT LABEL



1.63
[41.5]



CAD FILENAME/LAYERS M00884AA_DC_07A.PRT

												PANDUIT		CORP. TINLEY PARK, ILLINOIS			
												48 PORT UNDERFLOOR BOX (CUFB48BL) CUSTOMER DRAWING					
												UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ±.010 (.3) (.XX) ±.03 (.8) ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.			
DRAWN BY JSP												SCALE NONE		DRAWING NO. 00884-11		DWG SIZE A	
DATE 9-4-00																	
CHECKED BY PBD																	
REV	DATE	BY	CHK	DESCRIPTION	ECN	CHK	CUST	SUP									
I	6-11-01	JSP		A. REVISED SILKSCREEN.	00884-11												
R	9-4-00	JSP	PBD	RELEASED TO PRODUCTION.	00884-11	PBD											

+

+

+