


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

1. SEE SHEET 2 FOR PRODUCT DESCRIPTIONS AND TECHNICAL SPECIFICATIONS.
2. SEE CURRENT CATALOG FOR PATCH CORD/PIGTAIL LENGTHS AND PACKAGE QUANTITY.
3. FOR LENGTHS OTHER THAN THOSE LISTED IN CATALOG, CONTACT YOUR PANDUIT SALES PERSON.
4. TESTED TO EIA/TIA 568-B.3.
5. PATCH CORD ROUTING CONFIGURATION A TO B.
6. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.




LC CONNECTOR HOUSING KEY CONFIGURATIONS		
"A" BLACK	"B" RED	"C" GREEN
"D" YELLOW	"E" ORANGE	"F" DARK BLUE

FIBER OPTIC 900um BUFFERED KEYED LC PIGTAIL
CUSTOMER DRAWING



PANDUIT™
CORP.
TINLEY PARK, ILL 60477



ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED.
DIMENSIONAL TOLERANCES ARE:
(.X) ±.03 | (.XXX) ±.010 | (.3) ANGLES

DRAWING FILENAME: M02779CS_DC_00B.pr't
SCALE: NONE

DRAWN BY: MC

REVIEW DRAWING NUMBERS

PART NO. SEE TABLE, SHT. 2

DATE: 10-01-07

CHK'D: RAF



DRAWING NO. 02779-53 (SHT. 1 of 2) SIZE A

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
1	02-08-08	MC		RELEASED TO PRODUCTION	02779-53				

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FIBER OPTIC 900um BUFFERED KEYED LC PIGTAIL							
PANDUIT PART NO.	CABLE				KEYED LC CONNECTOR		
	FIBER TYPE	RATING	COUNT	COLOR	MAX. IL	MIN. RL	KEY/COLOR
F5B10A-NM** F5B10B-NM** F5B10C-NM** F5B10D-NM** F5B10E-NM** F5B10F-NM**	50/125um OM2	RISER (OFNR)	SIMPLEX 900um BUFFERED FIBER	BLUE	0.30dB	20dB	A/BLACK B/RED C/GREEN D/YELLOW E/ORANGE F/DK.BLUE
F6B10A-NM** F6B10B-NM** F6B10C-NM** F6B10D-NM** F6B10E-NM** F6B10F-NM**	62.5/125um OM1	RISER (OFNR)	SIMPLEX 900um BUFFERED FIBER	BLUE	0.30dB	20dB	A/BLACK B/RED C/GREEN D/YELLOW E/ORANGE F/DK.BLUE
FXB10A-NM** FXB10B-NM** FXB10C-NM** FXB10D-NM** FXB10E-NM** FXB10F-NM**	10 GbE 50/125um OM3	RISER (OFNR)	SIMPLEX 900um BUFFERED FIBER	BLUE	0.30dB	26dB	A/BLACK B/RED C/GREEN D/YELLOW E/ORANGE F/DK.BLUE
F9B10A-NM** F9B10B-NM** F9B10C-NM** F9B10D-NM** F9B10E-NM** F9B10F-NM**	9/125um OS1	RISER (OFNR)	SIMPLEX 900um BUFFERED FIBER	BLUE	0.35dB	55dB	A/BLACK B/RED C/GREEN D/YELLOW E/ORANGE F/DK.BLUE

** - DENOTES PATCH CORD LENGTH, WHERE M = METERS AND F = FEET

FIBER OPTIC 900um BUFFERED KEYED LC PIGTAIL									
CUSTOMER DRAWING									
 PANDUIT ™ CORP. TINLEY PARK, ILL 60477									
 THIRD ANGLE PROJECTION						ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ±.03 (.XXX) ±.010 (.3) ANGLES		DRAWING FILENAME M02779CS_DC_00B.prt	
DRAWN BY MC						REVIEW DRAWING NUMBERS		PART NO. SEE TABLE	
DATE 10-01-07						AS NOTED		DRAWING NO. 02779-53	
CHK'D RAF								SIZE A	
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
1	02-08-08	MC		RELEASED TO PRODUCTION	02779-53				