


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



ST CONNECTORS
DUST CAPS REMOVED

MT-RJ CONNECTOR
DUST CAP REMOVED

NOTES:

1. SEE CURRENT CATALOG FOR PACKAGE QUANTITY.
2. FOR LENGTHS OTHER THAN THOSE SHOWN, CONTACT YOUR PANDUIT SALES PERSON.
3. TESTED TO EIA/TIA 568-B.3.
4. PATCH CORD ROUTING CONFIGURATION A TO B.

PANDUIT PART NO.	DESCRIPTION	AVAILABLE LENGTHS
F6Z2-12M*	62.5/125um OR 50/125um MULTIMODE RISER RATED PATCH CORD ST TO MT-RJ	1, 2, 3, 5, & 10 METER
F5Z2-12M*		


COMPONENT	TYPE/DESCRIPTION	COLOR	MAXIMUM LOSS
CABLE	62.5 OR 50/125um 1.8mm ZIPCORD CABLE RISER RATED	ORANGE	
CONNECTORS	MULTIMODE ST (2)	RED/ BLACK	.35 dB
	MULTIMODE MT-RJ	BLACK	.35 dB

PANDUIT PART NO.	DESCRIPTION	AVAILABLE LENGTHS
F6LZ2-12M*	62.5/125um OR 50/125um MULTIMODE LS-ZH PATCH CORD ST TO MT-RJ	1, 2, 3, 5, & 10 METER
F5LZ2-12M*		


COMPONENT	TYPE/DESCRIPTION	COLOR	MAXIMUM LOSS
CABLE	62.5 OR 50/125um 1.8mm ZIPCORD CABLE LOW SMOKE-ZERO HALOGEN	ORANGE	
CONNECTORS	MULTIMODE ST (2)	RED/ BLACK	.35 dB
	MULTIMODE MT-RJ	BLACK	.35 dB

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
R	06-30-06	JH		RELEASED FOR PRODUCTION	02412-09				

FIBER OPTIC PATCH CORD
ST TO MT-RJ CONFIGURATION
CUSTOMER DRAWING



THIRD ANGLE
PROJECTION



PANDUITTM
CORP.
TINLEY PARK, ILL 60477

ALL DIMENSIONS ARE GIVEN IN INCHES
UNLESS OTHERWISE SPECIFIED.

DIMENSIONAL TOLERANCES ARE:
(.X) ±.03 | (.XXX) ±.010 | (.3) ±.010

(.XX) ±.03 | (.8) ±.010

DRAWING FILENAME
MO2412BR_DC_00A.prt

SCALE
NONE

PART NO.
SEE TABLE

DRAWING NO.
02412-09

SIZE
A

DRAWN BY: JH REVIEW DRAWING NUMBERS:

DATE: 06-22-06

CHK'D: