



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




**FRONT VIEW**  
SHOWN W/O DUSTCAPS


PANDUIT P/N	DESCRIPTION
FCZ-24-10BY	50/125 10GbE OM4 MULTIMODE 24 FIBER, MTP TO LC CASSETTE MODULE
FCZO-24-10BY	OPTIMIZED 50/125 10GbE OM4 MULTIMODE 24 FIBER, MTP TO LC CASSETTE MODULE


**NOTES:**

- SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
- SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
- MATERIALS:  
A. BOX AND LID: POWDER COATED ALUMINUM  
B. ADAPTER: COMPOSITE PLASTIC
- CASSETTE MODULE WEIGHT: 7.25oz (205.6g)
- DIMENSIONS IN BRACKETS ARE METRIC.



**PORT DESIGNATIONS**  
AS VIEWED FROM  
THE FRONT  
ADAPTERS REMOVED FOR CLARITY



										FIBER OPTIC CASSETTE MODULE FLIPPED 24 FIBER, LC TO MTP CONFIGURATION CUSTOMER DRAWING		
										 PANDUIT™ CORP. TINLEY PARK, ILL 60477		
										ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±.03   (.XXX) ±.010   (0.3)		
										DRAWING FILENAME MO2068AV_DC/00A		
										SCALE NONE		
										PART NO. SEE TABLE		
										DRAWING NO. 02068-64		
										SIZE A		
R	09-16-09	EFK		RELEASED TO PRODUCTION	02068-64						THIRD ANGLE PROJECTION	DATE 09-16-09
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	CHK'D	REVIEW DRAWING NUMBERS	