


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	KEY	COLOR	WEIGHT	FERRULE TYPE
FJEPGM5CZYL	Z	YELLOW	.10 LB/10 PCS. (44.5 G/10 PCS.)	ZIRCONIA (CERAMIC)

NOTES:


1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE PACKAGE QUANTITY.
2. OPTI-JACK ACCEPTS HIGH PERFORMANCE 62.5/125 MICRON AND 50/125 MICRON MULTIMODE GLASS OPTICAL FIBER CABLE.
3. DESIGNED FOR SIMPLE FIELD TERMINATION.
4. THE MAX. INSERTION LOSS PER CONNECTOR IS .75 dB. OPERATING TEMP. RANGE IS FROM -40° TO +70° C.
5. FULLY COMPLIES WITH THE FIBER OPTIC CONNECTOR PERFORMANCE REQUIREMENTS AS SPECIFIED IN TIA/EIA-568-A.
6. DIMENSIONS IN PARENTHESES ARE IN METRIC

KEYED "Z"
CONFIGURATION
SCALE: 2 : 1

OPTI-PLUG™ FJ KEYED "Z"
MULTIMODE CONNECTOR
CUSTOMER DRAWING



PANDUIT™
CORP.
TINLEY PARK, ILL 60477



ALL DIMENSIONS ARE GIVEN IN INCHES
UNLESS OTHERWISE SPECIFIED.
DIMENSIONAL TOLERANCES ARE:
(.X) ±.2 (5.0) (.XXX) ±.010 (0.3)
(.XX) ±.02 (0.5) ANGLES ±1°

DRAWING FILENAME
M00977A1_DC_00B.prt
SCALE
NONE

DRAWN BY
MC

REVIEW DRAWING NUMBERS

PART NO.
FJEPGM5CZYL

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
1	05-11-05	MYW		RELEASED TO PRODUCTION	00977-36				

DATE
07-10-01
CHK'D
JAW

SEE NOTES

DRAWING NO.
00977-36
SIZE
A