


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

**NOTES:**

1. DIAMETER DIMENSION, SHOWN FOR REFERENCE ONLY.
2. DIMENSIONS IN BRACKETS ( ) ARE ENGLISH.
3. ALL MATERIALS AND COMPONENTS USED MUST MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.




PART NUMBER	FIBER TYPE	JACKET RATING	JACKET COLOR
FLCR902Y	SINGLEMODE 9/125um	RISER	BLACK
FLCL902Y		LSZH	
FLCR602Y	MULTIMODE 62.5/125um	RISER	
FLCL602Y		LSZH	
FLCR502Y	MULTIMODE 50/125um	RISER	
FLCL502Y		LSZH	
FLCRX02Y	MULTIMODE 50/125um OM3	RISER	
FLCLX02Y		LSZH	
FLCRV02Y	MULTIMODE 50/125um OM3 150 METER LONG REACH	RISER	
FLCLV02Y		LSZH	
FLCRZ02Y	MULTIMODE 50/125um OM4	RISER	
FLCLZ02Y		LSZH	

TECHNICAL SPECIFICATIONS			
MAXIMUM LOSS - MULTIMODE		MAXIMUM LOSS - SINGLEMODE	
3.5 dB/KM @ 850nm 1.5 dB/KM @ 1300nm		.75 dB/KM @ 1310nm .75 dB/KM @ 1550nm	
BEND RADIUS		TENSILE LOAD	
INSTALLATION	LONG TERM	INSTALLATION	LONG TERM
230mm [9.0 in]	115mm [4.5 in]	1340 N [304 lbf]	400 N [90 lbf]
TEMPERATURE			
INSTALLATION/OPERATION		STORAGE	
-20° C TO +60° C -4° F TO +140° F		-40° C TO +65° C -40° F TO +149° F	

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
01	10-29-09	EFK		RELEASED TO PRODUCTION	02055-151				

OPTI-CORE 2 FIBER INDOOR-OUTDOOR CABLE  
CUSTOMER DRAWING



**PANDUIT**™  
CORP.  
TINLEY PARK, ILL 60477

DRAWING FILENAME  
M02055CZ\_DC\_02/00B

SCALE  
NONE

PART NO.  
FLCR\*02Y  
FLCL\*02Y

DRAWING NO.  
02055-151

SIZE  
A

ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.

DIMENSIONAL TOLERANCES ARE:  
(.X) (.XXX) ± 0.3 (.010)  
(.XX) ± 0.8 (.03) ANGLES

THIRD ANGLE PROJECTION

DRAWN BY: EFK  
DATE: 03-07-07  
CHK'D: WMA

REVIEW DRAWING NUMBERS