


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

1. DIAMETER DIMENSION, SHOWN FOR REFERENCE ONLY.
2. DIMENSIONS IN BRACKETS () ARE ENGLISH.
3. ALL MATERIALS AND COMPONENTS USED MUST MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.



PART NUMBER	FIBER TYPE	JACKET RATING	JACKET COLOR
FLCR904Y	SINGLEMODE 9/125um	RISER	BLACK
FLCL904Y		LSZH	
FLCR604Y	MULTIMODE 62.5/125um	RISER	
FLCL604Y		LSZH	
FLCR504Y	MULTIMODE 50/125um	RISER	
FLCL504Y		LSZH	
FLCRX04Y	MULTIMODE 50/125um OM3	RISER	
FLCLX04Y		LSZH	
FLCRV04Y	MULTIMODE 50/125um OM3 150 METER LONG REACH	RISER	
FLCLV04Y		LSZH	
FLCRZ04Y	MULTIMODE 50/125um OM4	RISER	
FLCLZ04Y		LSZH	


TECHNICAL SPECIFICATIONS			
MAXIMUM LOSS - MULTIMODE		MAXIMUM LOSS - SINGLEMODE	
3.5 dB/KM @ 850nm 1.5 dB/KM @ 1300nm		.75 dB/KM @ 1310nm .75 dB/KM @ 1550nm	
BEND RADIUS		TENSILE LOAD	
INSTALLATION	LONG TERM	INSTALLATION	LONG TERM
230mm [9.0 in]	115mm [4.5 in]	1340 N [304 lbf]	400 N [90 lbf]
TEMPERATURE			
INSTALLATION/OPERATION		STORAGE	
-20° C TO +60° C -4° F TO +140° F		-40° C TO +65° C -40° F TO +149° F	

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
01	10-29-09	EFK		RELEASED TO PRODUCTION	02055-152				

OPTI-CORE 4 FIBER INDOOR-OUTDOOR CABLE
CUSTOMER DRAWING



PANDUIT™
CORP.
TINLEY PARK, ILL 60477



ALL DIMENSIONS ARE GIVEN IN INCHES,
UNLESS OTHERWISE SPECIFIED.
DIMENSIONAL TOLERANCES ARE:
(.X) (.XXX) ± 0.3 (.010)
(.XX) ± 0.8 (.03) ANGLES

DRAWING FILENAME
M02055CZ_DC_04/00B

SCALE
NONE

DRAWN BY
EFK

REVIEW DRAWING NUMBERS

PART NO. FLCR*04Y
FLCL*04Y

DATE
03-07-07

DRAWING NO. 02055-152

CHK'D
WMA

SIZE
A