


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

1. DIAMETER DIMENSION SHOWN FOR REFERENCE ONLY.
2. DIMENSIONS IN BRACKETS [] ARE ENGLISH.
3. FOR PART NUMBERS AND LENGTHS OTHER THAN THOSE SHOWN, CONTACT YOUR PANDUIT SALES PERSON.




PART NUMBERS AVAILABLE	FIBER TYPE	JACKET RATING	COLOR
FLDR924Y	SINGLEMODE 9/125um	RISER	YELLOW
FLDL924Y		LSZH	
FLDR624Y	MULTIMODE 62.5/125um	RISER	ORANGE
FLDL624Y		LSZH	
FLDR524Y	MULTIMODE 50/125um	RISER	ORANGE
FLDL524Y		LSZH	
FLDRX24Y	MULTIMODE 50/125um OM3	RISER	AQUA
FLDLX24Y		LSZH	
FLDRV24Y	MULTIMODE 50/125um OM3 150 METER LONG REACH	RISER	AQUA
FLDLV24Y		LSZH	

TECHNICAL SPECIFICATIONS		
MAXIMUM LOSS - MULTIMODE 3.5 dB/KM @ 850nm 1.5 dB/KM @ 1300nm	BEND RADIUS	
	INSTALLATION 290 mm (11.4 in)	LONG TERM 145 mm (5.7 in)
MAXIMUM LOSS - SINGLEMODE .75 dB/KM @ 1310nm .75 dB/KM @ 1550nm	TENSILE LOAD	
	INSTALLATION 1320 N (300 lbf)	
TEMPERATURE		
INSTALLATION/OPERATION		STORAGE
0° C TO 50° C 32° F TO 158° F		-40° C TO +75° C -40° F TO +167° F

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
02	03-13-07	EFK		RELEASED TO PRODUCTION	02055-82				

**OPTI-CORE 24 FIBER DISTRIBUTION CABLE
WITH 900um TIGHT BUFFER
CUSTOMER DRAWING**



PANDUITTM
CORP.
TINLEY PARK, ILL 60477

DRAWING FILENAME
M02055CE_DC_24_01B.prt

SCALE
NONE

PART NO.
FLDR*24Y
FLDL*24Y

DRAWING NO.
02055-82

SIZE
A

ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.

DIMENSIONAL TOLERANCES ARE:
 (.X) (.XXX) ± .010 (0.3)
 (.XX) ± .03 (0.8) ANGLES

THIRD ANGLE PROJECTION

DRAWN BY: MC REVIEW DRAWING NUMBERS

DATE: 08-09-05

CHK'D: WMA