


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

1. DIAMETER DIMENSION SHOWN FOR REFERENCE ONLY.
2. DIMENSIONS IN BRACKETS [] ARE ENGLISH.
3. FOR PART NUMBERS AND LENGTHS OTHER THAN THOSE SHOWN, CONTACT YOUR PANDUIT SALES PERSON.




PART NUMBERS AVAILABLE	FIBER TYPE	JACKET RATING	COLOR
FLIR904Y	SINGLEMODE 9/125um	RISER	YELLOW
FLIL904Y		OFNR-LS	
FLIR604Y	MULTIMODE 62.5/125um	RISER	ORANGE
FLIL604Y		OFNR-LS	
FLIR504Y	MULTIMODE 50/125um	RISER	ORANGE
FLIL504Y		OFNR-LS	
FLIRX04Y	MULTIMODE 50/125um OM3	RISER	AQUA
FLILX04Y		OFNR-LS	
FLIRV04Y	MULTIMODE 50/125um OM3 150 METER LONG REACH	RISER	AQUA
FLILV04Y		OFNR-LS	

TECHNICAL SPECIFICATIONS		
MAXIMUM LOSS - MULTIMODE 3.5 dB/KM @ 850nm 1.5 dB/KM @ 1300nm	BEND RADIUS	
	INSTALLATION	LONG TERM
MAXIMUM LOSS - SINGLEMODE .75 dB/KM @ 1310nm .75 dB/KM @ 1550nm	TENSILE LOAD - PLENUM	
	INSTALLATION	LONG TERM
TEMPERATURE		
INSTALLATION/OPERATION		STORAGE
0° C TO 50° C 32° F TO 158° F		-40° C TO +75° C -40° F TO +167° F

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
R	03-14-07	EFK		RELEASED TO PRODUCTION	02055-145				

FIBER OPTIC SINGLE STRAND
4 FIBER DISTRIBUTION CABLE
CUSTOMER DRAWING



PANDUIT™
CORP.
TINLEY PARK, ILL 60477

DRAWING FILENAME
M02055CE_DC_04_00A.prt

SCALE
NONE

PART NO.
FLIL*04Y
FLIR*04Y

DRAWING NO.
02055-145

SIZE
A

ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.

DIMENSIONAL TOLERANCES ARE:
 (.X) ±.010 | (.XXX) ±.010 | (0.3) ±.010
 (.XX) ±.03 | (0.8) ±.03

THIRD ANGLE PROJECTION

DRAWN BY: EFK

DATE: 03-05-07

CHK'D: WMA

REVIEW DRAWING NUMBERS