


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	DESCRIPTION	COLOR	MAXIMUM LOSS
FODPX72Y FODRX72Y	MULTIMODE 50/125um 10GbE OM3	AQUA	3.5dB/KM @ 850nm 1.5dB/KM @ 1300nm
FODPZ72Y FODRZ72Y	MULTIMODE 50/125um 10GbE OM4		3.5dB/KM @ 850nm 1.5dB/KM @ 1300nm



PLENUM - FODPX72Y/FODPZ72Y			
TENSILE LOAD		BEND RADIUS	
INSTALLATION	LONG TERM	INSTALLATION	LONG TERM
660 N (150 lbf)	165 N (37.5 lbf)	410 mm (15.8 in)	201 mm (7.9 in)
CABLE DIAMETER (REFERENCE ONLY)	TEMPERATURE		
	INSTALLATION/OPERATION		STORAGE
20.1mm (0.79")	0°C TO +50°C 32°F TO +122°F		-40°C TO +65°C -40°F TO +149°F
RISER RATED - FODRX72Y/FODRZ72Y			
TENSILE LOAD		BEND RADIUS	
INSTALLATION	LONG TERM	INSTALLATION	LONG TERM
1320 N (300 lbf)	330 N (74 lbf)	440 mm (17.3 in)	220 mm (8.7 in)
CABLE DIAMETER (REFERENCE ONLY)	TEMPERATURE		
	INSTALLATION/OPERATION		STORAGE
22.0mm (0.87")	-20°C TO +50°C -4°F TO +122°F		-40°C TO +65°C -40°F TO +149°F

WEIGHT OF 2.5km REEL/BOX	
OFNP	OFNR
1179.3 kg (2599.9 lbs)	1213.6 kg (2675.5 lbs)

NOTES:

1. DIAMETER DIMENSION, SHOWN FOR REFERENCE ONLY.
2. CABLE SUPPLIED IN 2500 METER (8202 FT) LENGTHS.
3. FOR PART NUMBERS AND LENGTHS OTHER THAN THOSE SHOWN, CONTACT YOUR PANDUIT SALES PERSON.
4. ALL MATERIALS AND COMPONENTS USED MUST MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
02	10-21-09	EFK		RELEASED TO PRODUCTION	02055-53				

MULTIMODE 50/125um OPTI-CORE 10GbE OM3 & OM4 72 FIBER DISTRIBUTION CABLE WITH 900um TIGHT BUFFER CUSTOMER DRAWING											
 THIRD ANGLE PROJECTION		 PANDUIT™ CORP. TINLEY PARK, ILL 60477			ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) (.XXX)±0.3 (.010) (.XX)±0.8 (.03) ANGLES					DRAWING FILENAME M02055BH_DC_72-10G/00C SCALE NONE	
		DRAWN BY MC			REVIEW DRAWING NUMBERS					PART NO. FODP*72Y FODR*72Y	
		DATE 08-28-04								DRAWING NO. 02055-53	
		CHK'D WMA								SIZE A	