


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




VIEW SHOWN WITHOUT
DUSTCAPS INSTALLED

PANDUIT PART NUMBER	DESCRIPTION
FQ5-6-3	50/125 MULTIMODE 6 FIBER, SC TO MTP CASSETTE
FQ6-6-3	62.5/125 MULTIMODE 6 FIBER, SC TO MTP CASSETTE
FQX-6-3	50/125 10GbE MULTIMODE 6 FIBER, SC TO MTP CASSETTE
FQX0-6-3	OPTIMIZED 50/125 10GbE MULTIMODE 6 FIBER, SC TO MTP CASSETTE
FQ9-6-3	9/125 SINGLEMODE 6 FIBER, SC TO MTP CASSETTE


NOTES:

- SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
- SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PRODUCT
- MATERIALS:
 - MODULE MATERIAL: PLASTIC
 - ADAPTER: COMPOSITE PLASTIC
- CASSTTE MODULE WEIGHT: 2.6oz [75g]
- DIMENSIONS IN BRACKETS ARE METRIC




REV	DATE	BY	CHK	DESCRIPTION
R	09-19-08	EFK		RELEASED TO PRODUCTION

QUICKNET SFQ SERIES CASSETTE
6 FIBER, SC TO MTP CONFIGURATION
CUSTOMER DRAWING



THIRD ANGLE
PROJECTION



PANDUITTM
CORP.
TINLEY PARK, ILL 60477

ALL DIMENSIONS ARE GIVEN IN INCHES,
UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) (.XXX) ±.010 (0.3)
(.XX) ±.03 (0.8) ANGLES

DRAWING FILENAME
M02947AT_FQ-6-3_DC/00A.prt

SCALE
NONE

PART NO.
FQ*-6-3

DRAWING NO.
02947-31

SIZE
A

DRAWN BY: EFK REVIEW DRAWING NUMBERS

DATE: 09-19-08

CHK'D