




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

1. DIAMETER DIMENSION, SHOWN FOR REFERENCE ONLY.
2. DIMENSIONS IN BRACKETS [] ARE ENGLISH.
3. ALL MATERIALS AND COMPONENTS USED MUST MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.



TECHNICAL SPECIFICATIONS		
MAXIMUM LOSS		SINGLEMODE MAXIMUM LOSS
3.5 dB/KM @ 850nm 1.5 dB/KM @ 1300nm		.40 dB/KM @ 1310nm .30 dB/KM @ 1500nm
BEND RADIUS		
INSTALLATION		LONG TERM
31.8cm (12.4in)		15.9cm (6.2in)
TENSILE LOAD		
INSTALLATION		LONG TERM
2700 N (600 lbf)		890 N (200 lbf)
TEMPERATURE		
INSTALLATION	OPERATION	STORAGE
-30° C TO +60° C -22° F TO +140° F	-40° C TO +70° C -40° F TO +158° F	-40° C TO +75° C -40° F TO +167° F

										OUTSIDE PLANT SINGLE ARMOR-SINGLE JACKET CABLE WITH (6) 12 FIBER SUB-UNITS CUSTOMER DRAWING							
										 PANDUIT ™ CORP. TINLEY PARK, ILL 60477							
										 THIRD ANGLE PROJECTION ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) (.XXX)±0.3 (.010) (.XX)±0.8 (.03) ANGLES		DRAWING FILENAME M02055DA_DC_72/00C					
										DRAWN BY EFK		REVIEW DRAWING NUMBERS		SCALE NONE			
										DATE 07-10-07		PART NO. FSWN*72 FOWN*72		DRAWING NO.		SIZE	
										CHK'D WMA		02055-159		SHEET 1 OF 2		A	
REV	DATE	BY	CHK	DESCRIPTION			ECN	R	CUST	SUP	OTH						
02	10-29-09	EFK		RELEASED TO PRODUCTION			02055-159										

