

FEATURED



PSL-CB Circuit Breaker Lockout, Nylon, Red, 2.05"x0.75", PK1

PSL-CB

The PSL-CB Universal Circuit Breaker Lockout quickly locks out circuit breakers (such as 120/277V breakers) and is ideal for industrial and harsh applications. The compact, universal design fits a wide range of single, double, and triple handle circuit breakers. Accommodates breaker handles 0.30" – 0.60" (7.62 mm – 15.24 mm) tall and 0.25" – 0.44" (6.3 mm – 11.18 mm) thick. Nylon and Stainless Steel. 0.75" x 2.05" (19 mm x 52.1 mm). Color Red. 1 per package.

Specifications

Note	Single, double, and triple handle circuit breakers (poles) need a connecting bar that accepts a single lockout device.
Product Type	Circuit Breaker Lockout
Color	Red
Material	Nylon
Overall Length (In.)	2.05
Overall Length (mm)	52.1
Overall Width (In.)	0.75
Overall Width (mm)	19
Environment	Harsh Environment
Application	Quickly locks out circuit breakers (such as 120/277V breakers); ideal for industrial and harsh applications
Maximum Operating Temperature (°C)	121
Maximum Operating Temperature (°F)	250
Minimum Operating Temperature (°C)	-40
Minimum Operating Temperature (°F)	-40
Part Features	Fits single and multi-pole breakers

Packaging Detail

UPC	07498338637
Std. Pkg. Qty.	1
Std. Pkg. Volume (cf)	0.0051
Std. Ctn. Qty.	10
Std. Ctn. Volume (cf)	0.0509