



PSL-MLD Hasps, Galvanized Steel, Red, 5.9"x2.08", PK1

PSL-MLD

The PSL-MLD Multiple Lockout Device with Hasp can be used alone as a lockout hasp or with the provided 0.19" (4.8 mm) diameter cable to lockout electrical disconnects, gate valves, or large devices. Rugged polycarbonate and stainless steel provide strength, durability, added security, and corrosion resistance. Galvanized Steel with a vinyl coating. Jaw diameter 0.19" (4.8 mm). Includes 6.0' (1.8 m) vinyl-coated galvanized steel cable with loophole. Color Red. 1 per package.

Specifications

Note	Multiple lockout device; includes lockout hasp and 6.00' (1.8m) vinyl coated galvanized steel cable with loophole.
Color	Red
Finish/Coating	Vinyl
Material	Galvanized Steel
Product Type	Hasp
Jaw Diameter (In.)	0.19
Jaw Diameter (mm)	4.8
Number of Locks	6
Overall Length (In.)	5.9
Overall Length (mm)	149.9
Overall Width (In.)	2.08
Overall Width (mm)	52.8
Part Features	Easy to use

Packaging Detail

UPC	07498362679
Std. Pkg. Qty.	1
Std. Pkg. Volume (cf)	0.0167
Std. Ctn. Qty.	20
Std. Ctn. Volume (cf)	0.3338