

StrongHold offers a tailored selection of reliable, convenient and economical electrical products to support the way contractors work.

Not sure which grade of tape is necessary for your application?
Take a look at our chart to compare options.

Heavy Duty



ST88

Professional Grade



ST35



















ST43

General Purpose



ST14

ST17

	HEAVY DUTY	PROFESSIONAL	GENERAL PURPOSE
Thickness	 8.5 mil	 7.0 mil	 7.0 mil
Low temperature rating	 0°F -18°C	 0°F -18°C	 14°F -10°C
High temperature rating	 221°F 105°C	 221°F 105°C	 176°F 80°C
Sticking power	 2.2 N/cm TYP	 2.2 N/cm TYP	 1.6-1.8 N/cm
Elongation	 300% TYP	 260% TYP	 200% TYP
Breaking strength	 38 N/cm TYP	 30 N/cm TYP	 25 N/cm TYP
Color	