

Which Panduit PDU is Right For You?

In today's dynamic IT landscapes, efficiency and reliability aren't just goals – they're necessities. Our dynamic line of PDU solutions are engineered to elevate your operations, merging cutting-edge technology with uncompromised performance. **Which one best suits your needs?** The comparison chart below highlights the key features and benefits of our ES2P, G6, and EL2P PDUs.



Identify your ideal Panduit PDU here



Feature and Benefit	ES2P	G6	EL2P
Target Market	Entry to Mid-tier, cost-sensitive	AI workloads, hyperscale, colocation	AI workloads, hyperscale, colocation
Price Position	Budget-Friendly	Premium Intelligent Solution	Premium Intelligent Solution
Basic	✓	–	–
Monitored Input	✓	✓	✓
Monitored Switched	✓	✓	✓
Monitored Per Outlet	✓	✓	✓
Monitored & Switched Per Outlet	✓	✓	✓
Network Connectivity (10/100/1000)	Single Gigabit Ethernet, Serial	Single Gigabit Ethernet, Serial	Dual 1Gb Ethernet, Serial
Wi-Fi, Bluetooth	–	–	Yes (via CNT06)
Daisy Chain (Max)	16	32	64
Mixed Daisy Chaining	–	–	✓
Secure Zero Touch Provisioning (sZTP)	–	–	✓
Controller Interface Display	LCD	OLED	LCD Auto-rotating touchscreen
Colored Display	–	–	✓
Hot-Swappable Controller	Yes, Manually Rotatable	Yes, Manually Rotatable	Yes, Auto-Rotatable
Security	SNMPv3, TLS, encrypted protocols	SNMPv3, TLS, encrypted protocols	UL-2900-1, IEEE 802.1X, IEC 62443-4-2, USGv6, Secure Code Signing
DCIM Integration	–	–	Native Cisco Nexus Dashboard + Redfish API
Advanced DCIM Integration	–	–	✓
SiteCommand Compatibility	–	–	✓
Rack Access Control	–	✓	✓
Environmental Monitoring	✓	✓	✓
Outlet Type	C13/C19/NEMA 5-20R	C13/C19/NEMA 5-20R	Combination Outlets C13/C15/C19/C21, NEMA 5-20R
Outlet Switching	–	✓	MS/MSPO
Outlet Metering	✓	✓	✓
Metering Accuracy	± 2%	± 2%	± 0.5%
Swivel Cord	–	–	✓
Toolless Mounting (Vertical PDUs)	✓	✓	✓
Housing Material	Anodized Aluminum/ Powder Coated Steel	Powder Coated Steel	Powder Coated Steel
Operating Temperature (Max)	55°C	60°C	60°C
Warranty	3 Standard + 2 Year Extended	3 Standard + 2 Year Extended	5 Standard + 1 Year Extended
TAA Compliant (North America)	✓	–	✓

▶ For more information, visit panduit.com/pdu