



NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE PACKAGE QUANTITY.
2. THE FIBER-DUCT 2x2, 4x4 AND FIBERRUNNER 2x2 UNDER-FLOOR SUPPORT BRACKET IS USED TO SUPPORT THE FIBER-DUCT 2x2, 4x4 AND FIBERRUNNER 2x2 CABLE ROUTING SYSTEMS FROM 1" (25.4) DIAMETER OR 7/8" (22.2) SQUARE TUBE FLOOR PEDESTALS.
3. THE FIBER-DUCT 2x2, 4x4 AND FIBERRUNNER 2x2 UNDER-FLOOR SUPPORT BRACKET INCLUDES:
 ONE (1) BRACKET,
 TWO (2) 1/4-20x2x1 1/8x1 ROUND BEND U-BOLTS (FUSB ONLY),
 TWO (2) M6x1x50x28.6x24.6 ROUND BEND U-BOLTS (FUSBM ONLY),
 TWO (2) 1/4-20 HEX NUTS (FUSB ONLY),
 TWO (2) M6x1 (FUSBM ONLY),
 TWO (2) 1/4 HELICAL SPRING LOCKWASHERS (FUSB ONLY),
 TWO (2) M6 LOCKWASHERS (FUSBM ONLY),
 TWO (2) #10-32x1/2 PAN HEAD SLOTTED MACHINE SCREWS,
 TWO (2) #10 HELICAL SPRING LOCKWASHERS,
 TWO (2) #10-32 HEX MACHINE SCREW NUTS.
4. FINISH COLOR: YELLOW ZINC DICHROMATE (EXCEPT FOR HARDWARE)
5. DIMENSIONS IN PARENTHESES ARE IN METRIC.

PANDUIT PART NUMBER	WEIGHT
FUSB FUSBM	1.20 LB/EACH (543g/EACH)



ENG. REF.: D35245BQ_DC_FUSB_03.prt

CAD FILENAME/LAYERS: G FUSB.pdf

PANDUIT CORP TINLEY PARK, ILLINOIS
 FIBER-DUCT 2x2, 4x4 AND FIBERRUNNER 2x2
 UNDER-FLOOR SUPPORT BRACKET
 (FUSB, FUSBM)
 CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± (.XX) ± .03 (.8) ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY: TPC	MAT'L: STEEL	SCALE: NONE	
DATE: 11-18-96	J	DRAWING NO.: 35245-17	DWG SIZE: A
CHK'D: CEF			

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	GMBH
-	-----	---	---	J. REVISED MATERIAL I. REVISED PART WEIGHT	-----	--	--		
-	-----	---	---	H. REVISED GENERAL NOTES G. REVISED CAD FILENAME	-----	--	--		
3	12-28-06	MSO	RN	F. REVISED DRAWING TITLE E. REVISED AND REDRAWN	35245-17	RN	RN		