


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT * PART NUMBER	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	G in (mm)	H in (mm)	J in (mm)	WRITE-ON AREA in. (mm)	MINIMUM LOOP TENSILE lbs. (N)	CROSS-SECTION	WEIGHT (g) lbs./100 pcs.
	MIN (mm)	MAX (mm)													
BM1M	.18 (4.8)	0.90 (23)	.046 (1.2)	.095 (2.4)	.125 (3.2)	.156 (4.0)	.182 (4.6)	4.2 (107)	1.12 (28.5)	.31 (7.9)	.03 (.8)	.29 x 1.09 (7.4 x 27.7)	18 (80)	MINIATURE	.09 (40)
BM2M	.18 (4.8)	2.00 (51)	.046 (1.2)	.095 (2.4)	.125 (3.2)	.156 (4.0)	.182 (4.6)	7.9 (201)	1.12 (28.5)	.31 (7.9)	.03 (.8)		18 (80)	MINIATURE	.15 (69)

NOTES:

*SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

PANDUIT CORP. TINLEY PARK, ILLINOIS

DOME-TOP Barb Ty MARKER TIE
BM SERIES

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) \pm --- (.XXX) \pm .020 (.5)
(.XX) \pm .02 (.5) ANGLES \pm ---

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
JABO

MAT'L:

SCALE
NONE

5 12/1/04 ERW

REWORDED TITLE BLOCK

0248 5

DATE
5-30-97

NYLON 6.6

DRAWING NO.

BT-0248

REV DATE BY CHK

DESCRIPTION

ECN - R CUST SUP

CHK'D
JVL

DWG
A
SIZE