



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PART NO.	MATERIAL	MARKER SIZE inches [mm]	LABELS PER ROW
C150X025KBT	GMK4	1.500 [31.75]	2
C150X025KCT		0.250 [6.35]	



NOTES:
 1. SEE MFG. DRAWING NO. A61373.
 2. MILLIMETER ARE IN [].

CAD FILENAME/LAYERS
 100472NB_C10451_C150X025KBT_00.prt

PANDUIT CORP. TINLEY PARK, ILLINOIS

CUSTOMER DRAWING
 OPTIMUM C150X025KBT
 THERMAL TRANSFER LABELS

UNLESS OTHERWISE SPECIFIED,
 DIMENSIONAL TOLERANCES ARE:
 (.X) ± .031 (.XXX) ± .010
 (.XX) ± .015 ANGLES ±

UNLESS OTHERWISE SPECIFIED,
 ALL DIMENSIONS ARE GIVEN
 IN INCHES, THIRD ANGLE PROJECTION.

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
1	4/16/07	RVU		ADDED P/N: C150X025KCT. C150X025KBT MAT'L SHOULD BE GMK4.	4954	R		
0	8-23-06	RVU		DRAWING RELEASE	0000	R		

DRAWN BY RVU	MAT'L: SEE TABLE	SCALE NTS
DATE 8-23-06		DRAWING NO. C10451
CHK'D		DWG A SIZE