



Mini-Com® Stainless Steel Faceplates

- Accept Mini-Com® Modules for STP and UTP, fiber optic, and audio/video, which snap in and out for easy moves, adds, and changes
- Impact-resistant 304 stainless steel suitable for light industrial environments
- Optional adhesive labels available



CFP2SY



CFP4SY



CFP6SY



CFP4S-2GY



CFP8S-2GY



CFP10S-2GY

Part Number	Part Description	Std. Pkg. Qty.	Std. Ctn. Qty.
CFP2SY	Single gang, vertical faceplate accepts two Mini-Com® Modules.	1	10
CFP4SY	Single gang, vertical faceplate accepts four Mini-Com® Modules. Requires minimum 1.9" wide electrical box for proper mounting.	1	10
CFP6SY	Single gang, vertical faceplate accepts six Mini-Com® Modules. Requires minimum 1.9" wide electrical box for proper mounting.	1	10
CFP4S-2GY	Double gang, vertical faceplate accepts four Mini-Com® Modules.	1	10
CFP8S-2GY	Double gang, vertical faceplate accepts eight Mini-Com® Modules.	1	10
CFP10S-2GY	Double gang, vertical faceplate accepts ten Mini-Com® Modules.	1	10

All faceplates include mounting screws.

Component Labels for Mini-Com® Stainless Steel Faceplates



Faceplate Part Number	Suggested Label Solutions for TIA/EIA-606-A Compliance			
	Laser/Ink Jet Desktop Printer Label	TDP43ME Thermal Transfer Desktop Printer Label	PanTher™ LS8E Hand-Held Printer Label	Cougar™ LS9 Hand-Held Printer Label
CFP2SY	C061X030FJJ	C061X030YPT	C061X030FJC	T031X000FJC-BK
CFP4SY				
CFP4S-2GY	C188X030FJJ	C188X030YPT	C188X030FJC	T031X000FJC-BK
CFP6SY				
CFP8S-2GY	C125X030FJJ	C125X030YPT	C125X030FJC	T031X000FJC-BK
CFP10S-2GY	C315X030FJJ	C315X030YPT	C315X030FJC	T031X000FJC-BK

For complete labeling solutions and product information, reference charts on pages O.1 – O.22 of SA-NCCB51.