



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
CPP48FM6BL	12.8 LB/10 PCS (5785.7 g/10 PCS)

NOTES:

- SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS WITH THIS WIRING SYSTEM.
- THE FLUSH MOUNT PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
- PACKAGE CONTENTS:  
 (1) - 48 PORT STAMPING  
 (4) - 12 POSITION FACEPLATE (ASSEMBLED TO PANEL)  
 (1) - SCREW KIT (INCLUDES FOUR #12-24 SCREWS)  
 (1) - SCREW KIT (INCLUDES FOUR M6 SCREWS)
- DIMENSIONS IN PARENTHESIS ARE IN METRIC.



PART NUMBER	CPP48FM6BL	PRODUCT SPEC/PKG SPEC	N/A
I.I. NUMBER	N/A	WORK INSTRUCTION	N/A
TITLE			
<b>MINI-COM 48 PORT FLUSH MOUNT 6-PACK MODULAR PATCH PANEL</b>			
CUSTOMER DRAWING			
ITEM REVISION NAME		M01667AI/00	
DATASET FILE NAME		M01667AI_DC21/00A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.x ± .1 [ 2.54 ]      .xxx ± .005 [ .127 ]		<b>PANDUIT</b> PANEL: 18 GAGE GALVANNEALED- BLACK PAINT WITH WHITE LETTERING	
.xx ± .01 [ .25 ]      ANGLES ± 5 °			
DRAWN BY		DRAWING NUMBER:	
BJN		01667-21	
DATE		THIRD ANGLE PROJECTION	
1-9-14		SHT 1 OF 1	
CHK	JAV	SCALE	N/A
APR		SIZE	A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
R	1-9-14	BJN	JAV	MMR	RELEASED TO PRODUCTION	01667-21

D101000DA/14

2

1

2

1