


2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
EFPK-XY	.20 LB/10 PCS (90.7 g/10 PCS)



- NOTES:
1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
 2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.

PART NUMBER		EFPK - XY	
TITLE			
SINGLE GANG FACEPLATE LABEL KIT			
CUSTOMER DRAWING			
ITEM REVISION NAME		M02479IV/00	
DATASET FILE NAME		M02479IV_DC232/00B	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.x ± .xx ± .03 [.8]		.xxx ± .010 [.3]	
ANGLES ±		DRAWING NUMBER:	
THIRD ANGLE PROJECTION		02479-232	
DRAWN BY	DATE	CHK	SCALE
JSP	4-19-06	MJD	NONE
SHT 1 OF 1			SIZE
			A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
1	5/29/14	JSP	REFR	MMR	A. REVISED DRAWING TITLE BLOCK.	02479-232
R	4-19-06	JSP	MJD	MJD	RELEASED TO PRODUCTION	2479-232

2

1

D10100DA/14