

NOTES:

1. SEE SHEET 2 FOR PRODUCT DESCRIPTIONS AND TECHNICAL SPECIFICATIONS.
2. SEE CURRENT CATALOG FOR PATCH CORD LENGTHS AND PACKAGE QUANTITY.
3. FOR LENGTHS OTHER THAN THOSE LISTED IN CATALOG, CONTACT YOUR PANDUIT SALES PERSON.
4. TESTED TO EIA/TIA 568-B.3.
5. PATCH CORD ROUTING CONFIGURATION A TO B.
6. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.


LC CONNECTOR HOUSING KEY CONFIGURATIONS		
"A" BLACK	"B" RED	"C" GREEN
"D" YELLOW	"E" ORANGE	"F" DARK BLUE

R	10-25-07	MC		RELEASED TO PRODUCTION	02779-55						
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH		

FIBER OPTIC PATCH CORD
 DUPLEX KEYED LC TO LC CONFIGURATION
 CUSTOMER DRAWING



PANDUIT™
 CORP.
 TINLEY PARK, ILL 60477



ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED.
 DIMENSIONAL TOLERANCES ARE:
 (.X) ±.03 | (.XXX) ±.010 | (.3) ANGLES

DRAWING FILENAME: M02779CU_DC_00A.prp
 SCALE: NONE

DRAWN BY: MC
 DATE: 10-01-07
 CHK'D:

REVIEW DRAWING NUMBERS:



PART NO.: SEE TABLE, SHT. 2
 DRAWING NO.: 02779-55 (SHT. 1 of 2)
 SIZE: A

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

DUPLEX KEYED LC TO LC FIBER OPTIC PATCH CORD

PANDUIT PART NO.	CABLE				KEYED LC CONNECTOR			LC CONNECTOR		
	FIBER TYPE	RATING	COUNT	COLOR	MAX. IL	MIN. RL	KEY/COLOR	MAX. IL	MIN. RL	COLOR
F5E10A-10M** F5E10B-10M** F5E10C-10M** F5E10D-10M** F5E10E-10M** F5E10F-10M**	50/125um OM2	RISER (OFNR)	DUPLEX 1.6mm ZIPCORD	ORANGE	0.30dB	20dB	A/BLACK B/RED C/GREEN D/YELLOW E/ORANGE F/DK.BLUE	0.30dB	20dB	ELECTRIC IVORY
F6E10A-10M** F6E10B-10M** F6E10C-10M** F6E10D-10M** F6E10E-10M** F6E10F-10M**	62.5/125um OM1	RISER (OFNR)	DUPLEX 1.6mm ZIPCORD	ORANGE	0.30dB	20dB	A/BLACK B/RED C/GREEN D/YELLOW E/ORANGE F/DK.BLUE	0.30dB	20dB	ELECTRIC IVORY
FXE10A-10M** FXE10B-10M** FXE10C-10M** FXE10D-10M** FXE10E-10M** FXE10F-10M**	10 GbE 50/125um OM3	RISER (OFNR)	DUPLEX 1.6mm ZIPCORD	AQUA	0.30dB	20dB	A/BLACK B/RED C/GREEN D/YELLOW E/ORANGE F/DK.BLUE	0.30dB	26dB	ELECTRIC IVORY
F9E10A-10M** F9E10B-10M** F9E10C-10M** F9E10D-10M** F9E10E-10M** F9E10F-10M**	9/125um OS1	RISER (OFNR)	DUPLEX 1.6mm ZIPCORD	YELLOW	0.35dB	55dB	A/BLACK B/RED C/GREEN D/YELLOW E/ORANGE F/DK.BLUE	0.35dB	55dB	BLUE

** - DENOTES PATCH CORD LENGTH, WHERE M = METERS AND F = FEET

										FIBER OPTIC PATCH CORD DUPLEX KEYED LC TO LC CONFIGURATION CUSTOMER DRAWING			
										 PANDUIT ™ CORP. TINLEY PARK, ILL 60477			
										 THIRD ANGLE PROJECTION			
										ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ±.03 (.XXX) ±.010 (.3) ±.010 ANGLES			
										DRAWING FILENAME M02779CU_DC_00A.prt			
										SCALE NONE			
										PART NO. SEE TABLE			
R	10-25-07	MC	RELEASED TO PRODUCTION				02779-55			DATE 10-01-07	AS NOTED	DRAWING NO. 02779-55 (SHT. 2 of 2)	SIZE A
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	CHK'D			