


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

1. DIAMETER DIMENSION SHOWN FOR REFERENCE ONLY.
2. DIMENSIONS IN BRACKETS [] ARE ENGLISH.
3. FOR PART NUMBERS AND LENGTHS OTHER THAN THOSE SHOWN, CONTACT YOUR PANDUIT SALES PERSON.



PART NUMBERS AVAILABLE	FIBER TYPE	JACKET RATING	COLOR
FLDR948Y	SINGLEMODE 9/125um	RISER	YELLOW
FLDL948Y		LSZH	
FLDR648Y	MULTIMODE 62.5/125um	RISER	ORANGE
FLDL648Y		LSZH	
FLDR548Y	MULTIMODE 50/125um	RISER	ORANGE
FLDL548Y		LSZH	
FLDRX48Y	MULTIMODE 50/125um OM3	RISER	AQUA
FLDLX48Y		LSZH	
FLDRV48Y	MULTIMODE 50/125um OM3 150 METER REACH	RISER	AQUA
FLDLV48Y		LSZH	

TECHNICAL SPECIFICATIONS		
MAXIMUM LOSS - MULTIMODE 3.5 dB/KM @ 850nm 1.5 dB/KM @ 1300nm	BEND RADIUS	
	INSTALLATION 360 mm (14.2 in)	LONG TERM 180 mm (7.1 in)
MAXIMUM LOSS - SINGLEMODE .75 dB/KM @ 1310nm .75 dB/KM @ 1550nm	TENSILE LOAD - RISER	
	INSTALLATION 1320 N (300 lbf)	
TEMPERATURE		
INSTALLATION/OPERATION	STORAGE	
0° C TO 50° C 32° F TO 158° F	-40° C TO +75° C -40° F TO +167° F	

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	OPTI-CORE 48 FIBER DISTRIBUTION CABLE W/900um TIGHT BUFFER CUSTOMER DRAWING	
02	03-14-07	EFK		RELEASED TO PRODUCTION	02055-84					 PANDUIT ™ CORP. TINLEY PARK, ILL 60477	
										 THIRD ANGLE PROJECTION	ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) (.XXX) ± .010 (0.3) (.XX) ± .03 (0.8) ANGLES
										DRAWING FILENAME M02055CF_DC_48_01B.prt SCALE NONE	PART NO. FLDR*48Y FLDL*48Y
										DRAWING NO. 02055-84	SIZE A
										DRAWN BY MC	REVIEW DRAWING NUMBERS
										DATE 08-08-05	
										CHK'D WMA	