


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

1. DIAMETER DIMENSION, SHOWN FOR REFERENCE ONLY.
2. DIMENSIONS IN BRACKETS [] ARE ENGLISH.
3. ALL MATERIALS AND COMPONENTS USED MUST MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.



TECHNICAL SPECIFICATIONS		
MAXIMUM LOSS		SINGLEMODE MAXIMUM LOSS
3.5 dB/KM @ 850nm 1.5 dB/KM @ 1300nm		.40 dB/KM @ 1310nm .30 dB/KM @ 1500nm
BEND RADIUS		
INSTALLATION		LONG TERM
23.4cm [9.2in]		11.7cm [4.6in]
TENSILE LOAD		
INSTALLATION		LONG TERM
2700 N (600 lbf)		1800 N (400 lbf)
TEMPERATURE		
INSTALLATION	OPERATION	STORAGE
-10° C TO +60° C 4° F TO +140° F	-30° C TO +70° C -22° F TO +158° F	-40° C TO +70° C -40° F TO +158° F

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	TITLE	ITEM REVISION NAME	DATASET FILE NAME	PART NO.	DRAWING NUMBER:	SIZE
00	02-13-14	SAT	WMA	TCB	RELEASED TO PRODUCTION	M02055JY-DC	36, 48, 72 FIBER OUTSIDE PLANT UNARMORED CABLE WITH UP TO (6) 12 FIBER SUB-UNITS	M02055JY/00	M02055JY_DC/00A	SEE TABLE	M02055JY-DC	A
							CUSTOMER DRAWING		PANDUIT			
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		DRAWING NUMBER:			
							.x ± .xxx ± .010 [0.3]		DRAWING NUMBER:			
							.xx ± .03 [0.8] ANGLES ±		DRAWING NUMBER:			
							THIRD ANGLE PROJECTION		DRAWING NUMBER:			
							DRAWN BY: SAT		SCALE: NONE		SHT 1 OF 2	
							DATE: 02-13-14		SCALE: NONE		SHT 1 OF 2	
							CHK: WMA		SCALE: NONE		SHT 1 OF 2	
							SCALE: NONE		SCALE: NONE		SHT 1 OF 2	

