


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

- NOTES:
1. DIAMETER DIMENSION, SHOWN FOR REFERENCE ONLY.
  2. DIMENSIONS IN BRACKETS [ ] ARE ENGLISH.
  3. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.



TEMPERATURE	
PLENUM	
OPERATION/STORAGE	INSTALLATION
-40° F TO 176° F [ -40° C TO 80° C ]	32° F TO 140° F [ 0° C TO 60° C ]
RISER	
OPERATION/STORAGE	INSTALLATION
-40° F TO 176° F [ -40° C TO 80° C ]	14° F TO 140° F [ -10° C TO 60° C ]

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00	02-05-14	SAT	WMA	TCB	RELEASED TO PRODUCTION	M02055JP-DC

TITLE			
96 FIBER ARMORED INDOOR/OUTDOOR CABLE WITH 900µm BUFFERED FIBERS			
CUSTOMER DRAWING			
ITEM REVISION NAME		M02055JP/00	
DATASET FILE NAME		M02055JP_DC/00A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]		PART NUMBER:	
.x ±	.xxx ± .010 [ 0.3 ]	SEE TABLE	
.xx ± .03 [ 0.8 ]	ANGLES ±		
DRAWN BY		DRAWING NUMBER:	
SAT		M02055JP-DC	
DATE		SCALE	
02-05-14		NONE	
CHK		SIZE	
WMA		A	
THIRD ANGLE PROJECTION		SHT 1 OF 2	

