


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



CABLE DESCRIPTION
FIBER OPTIC SINGLE STRAND
DISTRIBUTION CABLE



PART NUMBERS AVAILABLE	FIBER TYPE	JACKET RATING	COLOR
FPDL924	SINGLEMODE 9/125 μ	LSZH	YELLOW
FPDL624	MULTIMODE 62.5/125	LSZH	ORANGE
FPDL524	MULTIMODE 50/125	LSZH	ORANGE
FODLX24	MULTIMODE 50/125 OM3	LSZH	AQUA
FODLZ24	MULTIMODE 50/125 OM4	LSZH	AQUA

TECHNICAL SPECIFICATIONS

MULTIMODE MAXIMUM LOSS	BEND RADIUS	
3.5 dB/KM @ 850nm 1.5 dB/KM @ 1300nm	INSTALLATION 230 mm (9.1 in)	LONG TERM 115 mm (4.5 in)
SINGLEMODE MAXIMUM LOSS	TENSILE LOAD - LSZH RATED	
.75 dB/KM @ 1310nm .75 dB/KM @ 1500nm	INSTALLATION 800 N (180 lbf)	LONG TERM 400 N (90 lbf)
TEMPERATURE		
INSTALLATION -20° C TO +70° C -4° F TO +158° F	OPERATION -20° C TO +70° C -4° F TO +158° F	STORAGE -40° C TO +75° C -40° F TO +167° F

NOTES:

- DIAMETER DIMENSION SHOWN FOR REFERENCE ONLY.
- DIMENSIONS IN BRACKETS [] ARE ENGLISH.
- FOR PART NUMBERS AND LENGTHS OTHER THAN THOSE SHOWN, CONTACT YOUR PANDUIT SALES PERSON.

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	FIBER OPTIC SINGLE STRAND 24 FIBER DISTRIBUTION CABLE CUSTOMER DRAWING	
01	08-17-11	EFK	WMA	RELEASED TO PRODUCTION	02432-14	WMA	TCB			 PANDUIT ™ CORP. TINLEY PARK, ILL 60477	
										 THIRD ANGLE PROJECTION ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) (.XXX) ±.010 (.0.3) (.XX) ±.03 (.0.8) ANGLES	DRAWING FILENAME MO2432BC_DC_24/00B
										SCALE NONE	
										PART NO. FPDL*24	
										DRAWING NO. 02432-14	
										SIZE A	
										DRAWN BY: JH DATE: 11-17-05 CHK'D: EFK REVIEW DRAWING NUMBERS:	