

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	DESCRIPTION	FIBER COUNT	FIBER PER TUBE	NO. OF FILLER TUBES	MINIMUM BEND RADIUS	TENSILE LOAD (INSTALLATION)	TENSILE LOAD (LONG TERM)	COMPRESSIVE STRENGTH	ATTENUATION
FPTN606	MULTIMODE 62.5/125 OM1 UNARMORED STRANDED OUTSIDE PLANT CABLE	2	6	5	160mm	1800 N	1200 N	3000 N	3.5dB/km @ 850nm 1.0dB/km @ 1300nm
FPTN608		8	8						
FPTN612		12	12	4					
FPTN624		24		3					
FPTN636		36		2					
FPTN648		48		0					
FPTN672		72							
FPTN506	MULTIMODE 50/125 OM2 UNARMORED STRANDED OUTSIDE PLANT CABLE	2	6	5					
FPTN508		8	8						
FPTN512		12	12	4					
FPTN524		24		3					
FPTN536		36		2					
FPTN548		48		0					
FPTN572		72							
FQTNX06	MULTIMODE 50/125 OM3 UNARMORED STRANDED OUTSIDE PLANT CABLE	2	6	5					
FQTNX08		8	8						
FQTNX12		12	12	4					
FQTNX24		24		3					
FQTNX36		36		2					
FQTNX48		48		0					
FQTNX72		72							
FQTNZ06	MULTIMODE 50/125 OM4 UNARMORED STRANDED OUTSIDE PLANT CABLE	2	6	5					
FQTNZ08		8	8						
FQTNZ12		12	12	4					
FQTNZ24		24		3					
FQTNZ36		36		2					
FQTNZ48		48		0					
FQTNZ72		72							
FPTN906	SINGLEMODE 9/125 UNARMORED STRANDED OUTSIDE PLANT CABLE	2	6	5					
FPTN908		8	8						
FPTN912		12	12	4					
FPTN924		24		3					
FPTN936		36		2					
FPTN948		48		0					
FPTN972		72							

B

B

←

→

A

A

						TITLE STRANDED OUTSIDE PLANT FIBER OPTIC CABLE WITH UP TO 72 FIBERS CUSTOMER DRAWING						
						ITEM REVISION NAME M02432CV/00						
						DATASET FILE NAME M02432CV_DC/00A						
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) .x ± .xxx ± .010 (0.3) .xx ± .03 (0.8) ANGLES ±						
						PART NO. SEE TABLE						
						DRAWING NUMBER: M02432CV-DC						
00	02-05-14	SAT	WMA	TCB	RELEASED TO PRODUCTION	M02432CV-DC						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY SAT	DATE 02-05-14	CHK WMA	SCALE NONE	SHT 2 OF 2	SIZE A

