


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.






CABLE DESCRIPTION			
FIBER OPTIC MULTI SUB-UNIT DISTRIBUTION CABLE			
PART NUMBERS AVAILABLE	FIBER TYPE	JACKET RATING	COLOR
FPDL972	SINGLEMODE 9/125um	LSZH	YELLOW
FPDL672	MULTIMODE 62.5/125um	LSZH	ORANGE
FPDL572	MULTIMODE 50/125um	LSZH	ORANGE
FODLX72	MULTIMODE 50/125um OM3	LSZH	AQUA
FODLZ72	MULTIMODE 50/125um OM4	LSZH	AQUA

TECHNICAL SPECIFICATIONS		
MAXIMUM LOSS	BEND RADIUS	
3.5 dB/KM @ 850nm 1.5 dB/KM @ 1300nm	INSTALLATION	LONG TERM
	200 mm (7.9 in)	200 mm (7.9 in)
SINGLEMODE MAXIMUM LOSS	TENSILE LOAD - LSZH RATED	
.75 dB/KM @ 1310nm .75 dB/KM @ 1500nm	INSTALLATION	LONG TERM
	3600 N (810 lbf)	1800 N (405 lbf)
TEMPERATURE		
INSTALLATION	OPERATION	STORAGE
-20° C TO +70° C -4° F TO +158° F	-20° C TO +70° C -4° F TO +158° F	-40° C TO +70° C -40° F TO +158° F

NOTES:

1. DIAMETER DIMENSION SHOWN FOR REFERENCE ONLY.
2. DIMENSIONS IN BRACKETS ( ) ARE ENGLISH.
3. FOR PART NUMBERS AND LENGTHS OTHER THAN THOSE SHOWN, CONTACT YOUR PANDUIT SALES PERSON.

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
01	08-17-11	EFK	WMA	RELEASED TO PRODUCTION	02432-23	WMA	TCB		

FIBER OPTIC 72 FIBER DISTRIBUTION CABLE W/900um TIGHT BUFFER CUSTOMER DRAWING									
									
					ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) (.XXX) ± .010 (0.3) (.XX) ± .03 (0.8) ANGLES				
DRAWN BY: JH					DRAWING FILENAME: MO2432BE_DC_72/00B				
DATE: 11-16-05					SCALE: NONE				
CHK'D: WMA					PART NO.: FPDL*72				
					DRAWING NO.: 02432-23				
					SIZE: A				