

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	DESCRIPTION	FIBER COUNT	FIBER PER TUBE	NO. OF FILLER TUBES	MINIMUM BEND RADIUS	TENSILE LOAD (INSTALLATION)	TENSILE LOAD (LONG TERM)	COMPRESSIVE STRENGTH	ATTENUATION
FPTN606	MULTIMODE 62.5/125 OM1 UNARMORED STRANDED OUTSIDE PLANT CABLE	2	6	5	160mm	1800 N	1200 N	3000 N	3.5dB/km @ 850nm 1.0dB/km @ 1300nm
FPTN608		8	8						
FPTN612		12	12	4					
FPTN624		24							
FPTN636		36							
FPTN648		48							
FPTN672		72							
FPTN506	2	6	5						
FPTN508	8	8							
FPTN512	12	12	4						
FPTN524	24								
FPTN536	36								
FPTN548	48								
FPTN572	72								
FQTNX06	2	6	5						
FQTNX08	8	8							
FQTNX12	12	12	4						
FQTNX24	24								
FQTNX36	36								
FQTNX48	48								
FQTNX72	72								
FQTNZ06	2	6	5						
FQTNZ08	8	8							
FQTNZ12	12	12	4						
FQTNZ24	24								
FQTNZ36	36								
FQTNZ48	48								
FQTNZ72	72								
FPTN906	2	6	5						
FPTN908	8	8							
FPTN912	12	12	4						
FPTN924	24								
FPTN936	36								
FPTN948	48								
FPTN972	72								

B

B

←

→

A

A

						TITLE STRANDED OUTSIDE PLANT FIBER OPTIC CABLE WITH UP TO 72 FIBERS CUSTOMER DRAWING						
						ITEM REVISION NAME M02432CV/00						
						DATASET FILE NAME M02432CV_DC/00A						
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) .x ± .xxx ± .010 (0.3) .xx ± .03 (0.8) ANGLES ±						
						PART NO. SEE TABLE						
						DRAWING NUMBER: M02432CV-DC						
00	02-05-14	SAT	WMA	TCB	RELEASED TO PRODUCTION	M02432CV-DC						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	DRAWING NUMBER	SIZE
							SAT	02-05-14	WMA	NONE	SHT 2 OF 2	A