





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

| PANDUIT PART NUMBER | WEIGHT |
|---------------------|------------------------------|
| FRBC24X4 | 2.55 LB/EACH (1157g/EACH) |



NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. DIMENSIONS IN PARENTHESES ARE IN METRIC.



ENG. REF.: D39701BS_DC/00 FRBC24X4

CAD FILENAME/LAYERS: FRBC24X4.pdf

PANDUIT CORP TINLEY PARK, ILLINOIS
FIBERRUNNER 24x4 QUICKLOCK COUPLER (FRBC24X4)
 CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
 DIMENSIONAL TOLERANCES ARE:
 (.X) ± (.XXX) ±
 (.XX) ± .03 (.8) ANGLES ±

UNLESS OTHERWISE SPECIFIED,
 ALL DIMENSIONS ARE GIVEN IN
 INCHES, THIRD ANGLE PROJECTION.

| | | |
|----------------|----------------------|-----------------------|
| DRAWN BY: MSO | MAT'L: ABS AND STEEL | SCALE: NONE |
| DATE: 10-21-08 | | DRAWING NO.: 39701-14 |
| CHK'D: SL | | DWG SIZE: A |

| REV | DATE | BY | CHK | DESCRIPTION | ECN | R | CUST | SUP | GMBH |
|-----|----------|-----|-----|------------------------|----------|----|------|-----|------|
| R | 10-21-08 | MSO | SL | RELEASED TO PRODUCTION | 39701-14 | RN | RN | | |