




4x4 Routing System Roadmap




4x4 and 6x4 FiberRunner® Mounting Brackets




**FR6TB38 - Trapeze
QuikLock™ Bracket**
(page J.34)




**F2PCLB - Two-Piece
Ladder Rack Bracket
for Attaching
Threaded Rod to
1 1/2" - 2" Ladder Rack**
(page J.35)




**FR6LRB - Ladder Rack
QuikLock™ Bracket**
(page J.35)




**FR6LB - "L" Wall
Mount QuikLock™
Bracket** (page J.35)



- 1** FR4X4**6 – 4x4 FiberRunner® Channel (page J.40)




- 2** FRHC4**6 – 4x4 Snap-On Hinged Cover (page J.40)




- 3** FRSHC4**6 – 4x4 Split Hinged Cover (page J.40)




- 4** FRBC4X4** – 4x4 QuikLock™ Coupler (page J.41)




- 5** FRH454X4** – 4x4 Horizontal 45° Angle Fitting and FRH45SC4** Optional Split Cover (page J.41)




- 6** FRRA4X4** – 4x4 Horizontal Right Angle Fitting and FRRASC4** – Optional Split Cover (page J.41)



- 7** FRT4X4** – 4x4 Horizontal Tee Fitting and FRTSC4** – Optional Split Cover (page J.42)




- 8** FRFWC4X4** – 4x4 4-Way Cross Fitting and FRFWCSC4** – Optional Split Cover (page J.42)




- 9** FRVT4X4** – 4x4 QuikLock™ Vertical Tee (page J.44)




- 10** FRIV454X4** – 4x4 Inside Vertical 45° Angle Fitting (page J.42)




- 11** FRIVRA4X4** – 4x4 Inside Vertical 90° Angle Fitting (page J.42)



- 12** FROV454X4** – 4x4 Outside Vertical 45° Angle Fitting and FROV45SC4** – Optional Split Cover (pages J.42 and J.43)




- 13** FROVRA4X4** – 4x4 Outside Vertical Right Angle Fitting and FROVRASC4** – Optional Split Cover (page J.43)




- 14** FRCR4BL-X – Cable Retainer for 4x4 System (page J.40)




- 15** FREC4X4** – 4x4 End Cap Fitting (page J.42)




- 16** FRTR4X4** – 3-Sided BRC Trumpet Spillout for 4x4 FiberRunner® Exit (page J.46)




- 17** FR1.5IDE** – 1-Port Spillout Side Exit to 1.5" (38mm) Inside Diameter Corrugated Tubing (page J.46)



- 18** FRIDT4X4** – 2-Port Spillout to 1.5" (38mm) Inside Diameter Corrugated Tubing (page J.46)




- 19** FRSPJ2X2** – Spill-Over Junction with 2x2 Exit and FRSPJC24** – Optional Cover for 4x4 System (page J.45)




- 20** FRSPJ4X4** – Spill-Over Junction with 4x4 Exit and FRSPJC44** – Optional Cover for 4x4 System (pages J.45 and J.46)



- 21** FRUPS4X4** – 4x4 Up Spout (page J.46)



- 22** FRRF4FD2** – 4x4 FiberRunner® System to 2x2 Reducer Fitting with Cover (page J.43)



- 23** FRRF4FD4** – 4x4 FiberRunner® System to 4x4 Fiber-Duct™ Reducer Fitting with Cover (page J.43)



- 24** FRLPR42BL – Low Profile Reducer 4x4 to 2x2 for Vertical Tee (page J.44)

**Available colors include: YL (Yellow), OR (Orange), and BL (Black).
Note: Additional 6x4 and 4x4 bracket applications, see page J.23.