


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

1. DIAMETER DIMENSION SHOWN FOR REFERENCE ONLY.
2. CABLE IS LONGITUDINALLY WATER-BLOCKED.
3. PLENUM-RATED CABLES MEET THE REQUIREMENTS OF NFPA 262. RISER-RATED CABLES MEET THE REQUIREMENTS OF UL 1666.
4. ALL MATERIALS AND COMPONENTS USED MUST MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.



TEMPERATURE	
PLENUM	
OPERATION/STORAGE	INSTALLATION
-40° F TO 176° F [-40° C TO 80° C]	32° F TO 140° F [0° C TO 60° C]
RISER	
OPERATION/STORAGE	INSTALLATION
-40° F TO 176° F [-40° C TO 80° C]	14° F TO 140° F [-10° C TO 60° C]

						TITLE						
						2, 4 FIBER ARMORED INDOOR/OUTDOOR CABLE WITH 900µm BUFFERED FIBERS						
						CUSTOMER DRAWING						
						ITEM REVISION NAME		PANDUIT				
						M02055JK/00						
						DATASET FILE NAME		PART NUMBER: SEE TABLE				
						M02055JK_DC/00A						
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)						
						.x ± .xxx ± .010 (0.3)		DRAWING NUMBER: M02055JK - DC				
						.xx ± .03 (0.8) ANGLES ±						
00	02-03-14	SAT	WMA	TCB	RELEASED TO PRODUCTION	M02055JK - DC		THIRD ANGLE PROJECTION				
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 2	SIZE
							SAT	02-03-14	WMA	NONE		A

