


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



TECHNICAL SPECIFICATIONS			
MAXIMUM LOSS		SINGLEMODE MAXIMUM LOSS	
3.5dB/KM @ 850nm 1.5dB/KM @ 1300nm		.75dB/KM @ 1310nm .75dB/KM @ 1500nm	
TENSILE LOAD - OFCR		TENSILE LOAD - OFCP	
INSTALLATION	LONG TERM	INSTALLATION	LONG TERM
1320 N (300 lbf)	330 N (74 lbf)	660 N (150 lbf)	165 N (38 lbf)
	OFCR	OFCP	
OPERATION	-20° C TO +50° C (-4° F TO +122° F)		0° C TO +50° C (+32° F TO +122° F)
INSTALLATION			
STORAGE	-40° C TO +65° C (-40° F TO +149° F)		



NOTES:

1. DIAMETER DIMENSION, SHOWN FOR REFERENCE ONLY.
2. DIMENSIONS IN BRACKETS [] ARE ENGLISH.
3. BUFFER COLOR CODING AS SPECIFIED BY TIA/EIA-598
4. ALL MATERIALS AND COMPONENTS USED MUST MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.

										FIBER OPTIC ARMORED DISTRIBUTION CABLE WITH 24 FIBERS		CUSTOMER DRAWING			
												PANDUIT™ CORP. TINLEY PARK, ILL 60477			
												ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) (.XXX) ±0.3 (.010) (.XX) ±0.8 (.03) ANGLES		DRAWING FILENAME M02055BV_DC_24/02A	
										DRAWN BY MC		SCALE NONE			
										DATE 02-28-06		PART NO. FSP**24Y FOP**24Y			
										CHK'D WMA		DRAWING NO. 02055-104		SIZE A	
03	04-29-11	EFK		RELEASED TO PRODUCTION	02055-104										
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH						

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	FIBER TYPE	JACKET RATING	JACKET COLOR	DIAMETER	BEND RADIUS	
					INSTALLED	LONG TERM
FSPR924Y	SINGLEMODE 9/125	OFCR	YELLOW	17.5mm [0.689"]	47.3cm [18.6"]	23.7cm [9.33"]
FSP924Y		OFCP		14.8mm [0.583"]		
FSPR524Y	MULTIMODE 50/125	OFCR	ORANGE	17.5mm [0.689"]		
FSP524Y		OFCP		14.8mm [0.583"]		
FSPR624Y	MULTIMODE 62.5/125	OFCR	ORANGE	17.5mm [0.689"]		
FSP624Y		OFCP		14.8mm [0.583"]		
FOPRX24Y	MULTIMODE 50/125 OM3	OFCR	AQUA	17.5mm [0.689"]		
FOPPX24Y		OFCP		14.8mm [0.583"]		
FOPRZ24Y	MULTIMODE 50/125 OM4	OFCR	AQUA	17.5mm [0.689"]		
FOPPZ24Y		OFCP		14.8mm [0.583"]		

										FIBER OPTIC ARMORED DISTRIBUTION CABLE WITH 24 FIBERS CUSTOMER DRAWING	
										 PANDUIT ™ CORP. TINLEY PARK, ILL 60477	
										 THIRD ANGLE PROJECTION	
										ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) (.XXX)±0.3 (.010) (.XX)±0.8 (.03) ANGLES	
										DRAWING FILENAME M02055BV_DC_24/02A	
										SCALE NONE	
										PART NO. FSP**24Y FOP**24Y	
										DRAWING NO. 02055-104	
										SIZE A	
03	04-29-11	EFK		RELEASED TO PRODUCTION	02055-104						DATE 02-28-06
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	CHK'D	WMA