


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

1. DIAMETER DIMENSION, SHOWN FOR REFERENCE ONLY.
2. DIMENSIONS IN BRACKETS [] ARE ENGLISH.
3. ALL MATERIALS AND COMPONENTS USED MUST MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.




TECHNICAL SPECIFICATIONS		
MAXIMUM LOSS		SINGLEMODE MAXIMUM LOSS
3.5 dB/KM @ 850nm 1.5 dB/KM @ 1300nm		.40 dB/KM @ 1310nm .30 dB/KM @ 1500nm
BEND RADIUS		
INSTALLATION		LONG TERM
31.8cm (12.4in)		15.9cm (6.2in)
TENSILE LOAD		
INSTALLATION		LONG TERM
2700 N (600 lbf)		890 N (200 lbf)
TEMPERATURE		
INSTALLATION	OPERATION	STORAGE
-30° C TO +60° C -22° F TO +140° F	-40° C TO +70° C -40° F TO +158° F	-40° C TO +75° C -40° F TO +167° F

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
02	10-29-09	EFK		RELEASED TO PRODUCTION	02055-160				

OUTSIDE PLANT SINGLE ARMOR-SINGLE JACKET
CABLE WITH (8) 12 FIBER SUB-UNITS
CUSTOMER DRAWING



PANDUIT™
CORP.
TINLEY PARK, ILL 60477



ALL DIMENSIONS ARE GIVEN IN INCHES,
UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) (.XXX)±0.3 (.010)
(.XX)±0.8 (.03) ANGLES

DRAWING FILENAME
M02055DA_DC_96/00C
SCALE
NONE


DRAWN BY
EFK
DATE
07-10-07
CHK'D
WMA

REVIEW DRAWING NUMBERS

PART NO. FSWN*96
FOWN*96
DRAWING NO.
02055-160
SHEET 1 OF 2
SIZE
A

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	FIBER TYPE	FIBER COUNT	TUBE COUNT	DIAMETER
FSWN996	SINGLEMODE 9/125um	96	8 WITH 12 FIBERS	15.9mm [0.62"]
FSWN696	MULTIMODE 62.5/125um			
FSWN596	MULTIMODE 50/125um			
FOWNX96	MULTIMODE 50/125um OM3			
FOWNZ96	MULTIMODE 50/125um OM4			

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	OUTSIDE PLANT SINGLE ARMOR-SINGLE JACKET CABLE WITH (8) 12 FIBER SUB-UNITS CUSTOMER DRAWING	
02	10-29-09	EFK		RELEASED TO PRODUCTION	02055-160						
										 PANDUIT ™ CORP. TINLEY PARK, ILL 60477	
										ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) (.XXX)±0.3 (.010) (.XX)±0.8 (.03) ANGLES	
										DRAWING FILENAME M02055DA_DC_96/00C SCALE NONE	
										DRAWN BY EFK DATE 07-10-07 CHECK'D WMA	
										REVIEW DRAWING NUMBERS PART NO. FSWN*96 FOWN*96 DRAWING NO. 02055-160 SHEET 2 OF 2 SIZE A	