





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

DUPLEX SC TO KEYED LC FIBER OPTIC PATCH CORD

PANDUIT PART NO.	CABLE				SC CONNECTORS			KEYED LC CONNECTORS		
	FIBER TYPE	RATING	COUNT	COLOR	MAX. IL	MIN. RL	COLOR	MAX. IL	MIN. RL	KEY/COLOR
F5E3-10AM** F5E3-10BM** F5E3-10CM** F5E3-10MD** F5E3-10ME** F5E3-10MF**	50/125um OM2	RISER (OFNR)	DUPLEX 1.6mm ZIPCORD	ORANGE	0.30dB	20dB	ELECTRIC IVORY	0.30dB	20dB	A/BLACK B/RED C/GREEN D/YELLOW E/ORANGE F/DK.BLUE
F6E3-10AM** F6E3-10BM** F6E3-10CM** F6E3-10DM** F6E3-10EM** F6E3-10FM**	62.5/125um OM1	RISER (OFNR)	DUPLEX 1.6mm ZIPCORD	ORANGE	0.30dB	20dB	ELECTRIC IVORY	0.30dB	20dB	A/BLACK B/RED C/GREEN D/YELLOW E/ORANGE F/DK.BLUE
FXE3-10AM** FXE3-10BM** FXE3-10CM** FXE3-10DM** FXE3-10ME** FXE3-10MF**	10 GbE 50/125um OM3	RISER (OFNR)	DUPLEX 1.6mm ZIPCORD	AQUA	0.30dB	20dB	ELECTRIC IVORY	0.30dB	26dB	A/BLACK B/RED C/GREEN D/YELLOW E/ORANGE F/DK.BLUE
F9E3-10AM** F9E3-10BM** F9E3-10CM** F9E3-10DM** F9E3-10EM** F9E3-10FM**	9/125um OS1	RISER (OFNR)	DUPLEX 1.6mm ZIPCORD	YELLOW	0.75dB	55dB	BLUE	0.35dB	55dB	A/BLACK B/RED C/GREEN D/YELLOW E/ORANGE F/DK.BLUE

\*\* - DENOTES PATCH CORD LENGTH, WHERE M = METERS AND F = FEET

										FIBER OPTIC PATCH CORD DUPLEX SC TO KEYED LC CONFIGURATION CUSTOMER DRAWING			
										 <b>PANDUIT</b> ™ CORP. TINLEY PARK, ILL 60477			
										 THIRD ANGLE PROJECTION ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ±.03   (.XXX) ±.010   (.3) ±.010 (.XX) ±.03   (.8) ANGLES			
										DRAWING FILENAME M02779CR_DC_00A.prt			
										SCALE NONE			
										PART NO. SEE TABLE			
R	10-25-07	MC	RELEASED TO PRODUCTION			02779-51				DATE 10-01-07	AS NOTED	DRAWING NO. 02779-51 (SHT. 2 of 2)	SIZE A
REV	DATE	BY	CHK	DESCRIPTION			ECN	R	CUST	SUP	OTH	CHK'D	