











THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

# CURRENT PART NUMBERS

FEMALE TO FEMALE - MTP TO MTP FIBER OPTIC PATCH CORD							
PANDUIT PART NO.	CABLE				MTP CONNECTOR		
	RATING	FIBER TYPE	COUNT	COLOR	PERFORMANCE	POLARITY	BOOT COLOR
F5TRP5N5NAN*nnn	PLENUM (OFNP)	OM2	12	ORANGE	STANDARD	METHOD A	BLACK
FXTRP5N5NAN*nnn		OM3		AQUA	STANDARD		
FXTRP5N5NXN*nnn		OM3		AQUA	OPTIMIZED		
FZTRP5N5NAN*nnn		OM4		AQUA	STANDARD		
FZTRP5N5NXN*nnn		OM4		AQUA	OPTIMIZED		
FSTRP5N5NKN*nnn		OM4+		AQUA	ULTRA		
F9TRP5N5NAN*nnn		OS1		YELLOW	STANDARD		
F5TRL5N5NAN*nnn	LOW SMOKE ZERO HALOGEN (LSZH)	OM2	12	ORANGE	STANDARD	METHOD A	BLACK
FXTRL5N5NAN*nnn		OM3		AQUA	STANDARD		
FXTRL5N5NXN*nnn		OM3		AQUA	OPTIMIZED		
FZTRL5N5NAN*nnn		OM4		AQUA	STANDARD		
FZTRL5N5NXN*nnn		OM4		AQUA	OPTIMIZED		
FSTR5N5NKN*nnn		OM4+		AQUA	ULTRA		
F9TRL5N5NAN*nnn		OS1		YELLOW	STANDARD		

\*nnn - DENOTES PATCH CORD LENGTH, WHERE "\*" = "M" FOR METERS, "F" FOR FEET AND "nnn" FOR LENGTH

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	TITLE				DRAWING NUMBER:			
R	07-02-13	MC	JDK	SFDO	RELEASED TO PRODUCTION	10F093BC-DC	FIBER OPTIC MTP TO MTP ROUND CABLE PATCH CORD CUSTOMER DRAWING							
							ITEM REVISION NAME 10F093BC/00				MATERIAL: SEE NOTES SHEET 1			
							DATASET FILE NAME 10F093BC_DC/00A				UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)			
							.x ± .03 (0.8)      .xxx ± .010 (0.3) .xx ± .03 (0.8)      ANGLES ±				DRAWING NUMBER: 10F093BC-DC			
							 THIRD ANGLE PROJECTION				SHT 5 OF 7			
							DRAWN BY MC		DATE 05-16-13		CHK JDK		SCALE NONE	
											SIZE A			



