




TABLE 1				
PANDUIT PART NUMBER	FIBER TYPE	FIBER COUNT	MAX IL (dB)	MIN RL (dB)
FXTSLSE5EAAMLLL	50/125OM3	12	0.50	30
FZTSLSE5EAAMLLL	50/125 OM4			
FXUSLSE5EAAMLLL	50/125 OM3	24	0.50	30
FZUSLSE5EAAMLLL	50/125 OM4			

- NOTES:
1. MAXIMUM INSERTION LOSS IS 0.35 dB PER CONNECTOR.
  2. CONNECTOR MEETS THE REQUIREMENTS OF TIA-568-C.3.
  3. MPO POLARITY COMPLIES WITH METHOD "A" PER TIA-568-C.0
  4. LSZH-RATED CABLE ASSEMBLIES MEET IEC-60332, IEC-60754 AND IEC-61034 REQUIREMENTS.
  5. CABLE MEETS THE MECHANICAL REQUIREMENTS OF IEC60332-2 AND IEC60332-3 AND TELCORDIA GR-409-CORE.
  6. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
  7. MAXIMUM STRENGTH OF THE PULLING EYE IS 20 lbs.



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
R	03-11-13	SAT	WMA		RELEASED FOR CUSTOMER APPROVAL	12F178BG-DCA

PART NUMBER	SEE TABLE 1	PRODUCT SPECIFICATION	PS-NS-XXX; PPS-XXX
1:1 NUMBER	NS-XXXX	WORK IDENTIFICATION	AM-XXX; TM-XXX
TITLE	12 & 24 FIBER MPO TO MPO LSZH TRUNK CABLE WITH PULLING EYE		
ITEM REVISION NAME	CUSTOMER APPROVAL DRAWING		
DRAWING FILE NAME	12F178BG/00	<b>PANDUIT</b>	
DRAWING FILE NAME	12F178BG_DCA/00A		
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (IN 1 mm)			
.xx + .1 (2.54)	.xxx + .005 (.127)	THIRD ANGLE PROJECTION	
.xx + .01 (.254)	ANGLES ± 5°	DRAWING NUMBER: 12F178BG-DCA	
DRAWN BY	DATE	CHK	SCALE
SAT	03-11-13	WMA	NONE
SHT 1 OF 1			D